



Part Number : [465573145](#)

Product Description : SEARAY Slim Receptacle, 120 Circuits, 5.00mm Unmated Height, 4 Rows, with Pegs, Solder Charge Lead-Free

Series Number : 46557

Status : Active

Product Category : Board-to-Board Connectors



Documents & Resources

Drawings

[465573145 sd.pdf](#)

[PK-45971-002-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[SYM-46557-3145-001.zip](#)

[EE-45970-010-010.pdf](#)

[EE-46556-0085-001.pdf](#)

[SP-45970-010-010.zip](#)

[SP-46556-0085-001.zip](#)

Specifications

[AS-45970-001-001.pdf](#)

[AS-45970-002-001.pdf](#)

[AS-45970-990-001.pdf](#)

[PS-45970-001-001.pdf](#)


[TS-45970-001-001.pdf](#)

[TS-45970-002-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
------------	--------------

China RoHS	per SJ/T 11365-2006 
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Board-to-Board Connectors
Series	46557
Description	SEARAY Slim Receptacle, 120 Circuits, 5.00mm Unmated Height, 4 Rows, with Pegs, Solder Charge Lead-Free
Application	Board-to-Board, Signal, Mezzanine
Component Type	PCB Receptacle
Product Name	SEARAY
UPC	883906495558

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	2.7A
Grounding to PCB	No
Voltage - Maximum	240V AC

Physical

Circuits (Loaded)	120
Circuits (maximum)	120
Color - Resin	Black
Durability (mating cycles max)	100
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	None
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	1.515/g
Number of Rows	4
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	2.18mm
Pitch - Mating Interface	1.27mm
Pitch - Termination Interface	1.27mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes

Robotic Placement	Pick and Place Cap
Stackable	No
Temperature Range - Operating	-55° to +125°C
Termination Interface Style	Surface Mount
Unmated Height	5.00mm

Solder Process Data

Max-Duration	20
Lead-Free Process Capability	REFLOW
Max-Cycle	3
Max-Temp	260

Mates With / Use With

Mates with Part(s)

Description	Part Number
Searay Slim Plugs	<u>46556</u>