

U.I. Lapp GmbH	PRODUCT INFORMATION	
	SKINDICHT® ME-M	29.11.2013

Enables the use of cable glands with larger connection threads than the existing threaded holes



Assembly time



Space requirement



Reliability



Temperature-resistant

Application range

Machines
Devices
Housings

Design

Metric connection thread acc. to EN 50262

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

On request:	with O-ring fitted
Material:	Nickel-plated brass
Temperature range:	-60°C to +200°C

Product Management	Document: LAPP_PRO1037EN.pdf	1 / 2
--------------------	------------------------------	-------



Part number	Thread/ male M1	Thread/ female M2
SKINDICHT® ME-M		
52104450	12 x 1.5	16 x 1.5
52104452	16 x 1.5	20 x 1.5
52104454	20 x 1.5	25 x 1.5
52104456	25 x 1.5	32 x 1.5
52104458	32 x 1.5	40 x 1.5
52104460	40 x 1.5	50 x 1.5
52104462	50 x 1.5	63 x 1.5
SKINDICHT® ME-M hexagon		
52104463	63 x 1.5	75 x 1.5