

Eaton 160D200Q

Catalog Number: 160D200Q

Fuse-link, low voltage, 160 A, AC 500 V, D5, 56 x 46 mm, gR, DIN, IEC, fast-acting



General specifications

Product Name	Catalog Number
Eaton Bussmann series low voltage D fuse	160D200Q
	EAN
	5027590436953
Product Length/Depth	Product Height
56 mm	46 mm
Product Width	Product Weight
46 mm	224.6 g
Compliances	Certifications
CE	IEC/EN 60269-3
RoHS Compliant	VDE 0636
CE Marked	IEC 60269
	DIN EN 60269-3 (VDE 0636 Part 30)
	DIN EN 60269-1 (VDE 0636 Part 10)
	DIN VDE 0636-301

Product specifications

Type

Fuse

Application

For domestic and general industrial applications

Amperage Rating

160 A

Fuse size

DV

Current type

AC

Breaking capacity

50 kA

Frequency rating - max

62 Hz

Frequency rating - min

45 Hz

Construction size (fuse inserts)

DV

Rated voltage AC

500 V

Fuse type

D200Q - Fast acting

Accessory/spare part type

160GD200 Copper screw cap gauge piece

Utilization category

gR (general purpose semiconductor protection)

Color

Copper

Interrupt rating

50 kAIC

Fuse indicator

Non-indicating

Insulated metal gripping lugs (IMGL)

No

Connection

Resources

Brochures

[eaton-bussmann-series-d-and-d0-fuses-product-aid-pa132014en-en-us.pdf](#)

Catalogs

[CA134002EN](#)

Technical service bulletins

[Datasheet - 160D200Q](#)

Other

Construction size

DV

Fuse shape

Bottle

Response time

Fast-acting

Voltage type

AC

Suitable for

R2/DV Fuse base

Material

White ceramic body

Release characteristic

Fast (F)

Voltage rating

500 V

Fuse system (according to IEC 60269)

Other

Rated switching capacity AC

50 kA



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)