

## 249 - Standard drift punches





### Standards:

NF E 71-211, DIN 6450, ASME  
B107.410

### Description:

- Hexagonal shank, high-strength steel tip, hardened to 53-58 HRc.
- Zinc-plated finish.



	A [mm]	Diameter [mm]	Length L [mm]	Length L1 [mm]	Weight [g]
<b>249.10</b>	9.9	16.0	200.0	50.0	220.0
<b>249.2</b>	1.9	8.0	115.0	30.0	30.0
<b>249.3</b>	2.9	8.0	125.0	40.0	35.0
<b>249.4</b>	3.9	10.0	150.0	50.0	65.0
<b>249.5</b>	4.9	10.0	165.0	50.0	75.0
<b>249.6</b>	5.9	12.0	180.0	50.0	120.0
<b>249.8</b>	7.9	12.0	200.0	50.0	160.0