



FAG





3308-BD-XL-2HRS-TVH-C3

Angular contact ball bearing

Angular contact ball bearing 33...-BD-XL-2HRS-TVH, double row, X-life, seals, plastic cage

X-life

Technical information



Your current product variant

Design variant	B	Bearing without filling slot
Sealing	2HRS	Contact seal on both sides
Cage	TVH	Solid cage made of glass-fiber reinforced polyamid PA66
Tolerance class	P6	Class6 (P6), better than PN
Dimensional / heat stabilization	SN	Rings dimensional stabilized up to 120°
Lubricant	GA13	Ball bearing and insert bearing grease, standard for D>62mm
Axial internal clearance	C3	Group 3 (C3), bigger than CN

n.r.

	D	Design variant
≈m	0.978 kg	Weight

Main Dimensions & Performance Data

d	40 mm	Bore diameter
D	90 mm	Outside diameter
B	36.5 mm	Width
C _r	67,000 N	Basic dynamic load rating, radial
C _{0r}	48,500 N	Basic static load rating, radial
C _{ur}	3,350 N	Fatigue load limit, radial
n _G	6,000 1/min	Limiting speed



Mounting dimensions

$d_{a\min}$	49 mm	Minimum diameter shaft shoulder
$D_{a\max}$	81 mm	Maximum diameter of housing shoulder
$r_{a\max}$	1.5 mm	Maximum fillet radius







Dimensions

r_{\min}	1.5 mm	Minimum chamfer dimension
D_1	77.02 mm	Shoulder diameter outer ring
D_2	79.92 mm	Caliber diameter outer ring
d_1	58.99 mm	Shoulder diameter inner ring
d_2	56.82 mm	Caliber diameter inner ring
a	53.1 mm	Distance between the apexes of the pressure cones
α	30 °	Contact angle

Temperature range

T_{\min}	-20 °C	Operating temperature min.
T_{\max}	100 °C	Operating temperature max.

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Lifetime lubrication, freedom from maintenance
	Grease Lubrication
	Sealed on both sides