



Standard vernier caliper with 4-way measurement.



Features

- Four way measurement of inner and outer dimensions, step and depth
- Vernier scale for high resolution
- Chromed scale with laser engraved graduations
- Metric and imperial scales on both beam and vernier
- Locking screw for position hold
- Made of hardened alloyed Stainless Steel with micro-lapped measuring surfaces
- Standard DIN 862
- Supplied in a case



Model MW100-B

- Beam graduations in 1mm and 1/16th inches
- Vernier scale in 0.05mm and 1/128th inch

Model MW100-BI

- Beam graduations 1mm and 1/10th inch
- Vernier scale 0.02mm, 0.001 inch

Specification							
Code No	Range (mm)	Range (inch)	Accuracy (mm)	Resolution (mm)	Resolution (mm)	Dimension A (mm)	Dimension B (mm)
MW100-15B	0-150	0-6	±0.05	0.05	1/128	40	16
MW100-20B	0-200	0-8	±0.05	0.05	1/128	50	20
MW100-30B	0-300	0-12	±0.08	0.05	1/128	55	20
MW100-15BI	0-150	0-6	±0.02	0.02	0.001	40	16
MW100-20BI	0-200	0-8	±0.03	0.02	0.001	50	20
MW100-30BI	0-300	0-12	±0.04	0.02	0.001	55	20