



Specification
PC104/PC105
3-Phase Socket Tester



ELECTRICAL SPECIFICATIONS

Input voltage range: 380V to 415V AC (Phase to Phase)

Input frequency: 50Hz

Input current: < 20mA

GENERAL SPECIFICATIONS

Power: From circuit under test

Dimensions: 131(L) x 94(W) x 54(D) mm

Weight: Approx 292g (without plug)

Includes: Instructions

SAFETY:

Conforms to BS EN 61010-1, CAT III 300V

Class II Double Insulation

Pollution Degree: 2

EMC: Conforms to BS EN 61326-1

Check out what else you can get from Martindale:

- 17th Edition Testers
- Accessories
- Calibration Equipment
- Continuity Testers
- Electricians' Kits
- Environmental Products
- Full Calibration & Repair Service
- Fuse Finders
- Digital Clamp Meters
- Digital Multimeters
- Labels
- Microwave Leakage Detectors
- Motor Maintenance Equipment
- Multifunction Testers
- Non-trip Loop Testers
- Pat Testers & Accessories
- Phase Rotation Testers
- Proving Units
- Socket Testers
- Thermometers & Probes
- Test Leads
- Voltage Indicators
- Specialist Metrohm Testers (4 & 5kV)
- Specialist Drummond Testers



Martindale Electric Company Limited
Metrohm House, Imperial Park, Imperial Way, Watford, Hertfordshire, WD24 4PP
Tel: +44(0)1923 441717 Fax: +44 (0)1923 446900
E-mail: sales@martindale-electric.co.uk
Website: www.martindale-electric.co.uk

© 2012 Martindale Electric Company Ltd.

Registered in England No. 3387451. E. & O.E. Document Rev1 LITPC104/105