

CK2,5-ED-0,75BU AG - Crimp contact



1663653

<https://www.phoenixcontact.com/gb/products/1663653>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimp contact, contact diameter: 2.5 mm, turned, Socket, contact material: Copper alloy, contact surface: silver-plated, connection cross section: 0.75 mm² ... 0.75 mm², AWG 18

Commercial data

Item number	1663653
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	AF7AID
Product key	AF7AID
Catalog page	Page 509 (C-2-2019)
GTIN	4017918123468
Weight per piece (including packing)	1.598 g
Weight per piece (excluding packing)	1.59 g
Customs tariff number	85366990
Country of origin	DE

CK2,5-ED-0,75BU AG - Crimp contact



1663653

<https://www.phoenixcontact.com/gb/products/1663653>

Technical data

Notes

General	for HC-M-06..., HC-M-HV-, HC-M-08-, HC-M-20-, HC-A..., HC-B.., HC-BB..., HC-BBB..., and HC-HV contact carriers
---------	--

Mounting

Assembly note	The quality of a crimp connection is determined by DIN EN 60352-2.
---------------	--

Product properties

Product type	Crimp contact
Series	HC-M-06
	HC-M-HV
	HC-M-08
	HC-A
	HC-BB
	HC-B
	HC-HV
	HC-M-20
	HC-K
	HC-BBB
	HC-Q
	HC-COM
Type	Individual female contact
Contact material type	turned

Connection data

Connection method	Crimp connection
Contact connection type	Socket
Connection technology	Crimp connection
Conductor cross section	0.75 mm² ... 0.75 mm²
Connection cross section AWG	18
Stripping length of the individual wire	7.5 mm (9.5 mm at HC-M-HV...)
Conductor cross section flexible	0.75 mm² ... 0.75 mm²

Material specifications

Contact material	Copper alloy
Contact surface material	silver-plated

Dimensions

Mechanical characteristics

Contact diameter	2.5 mm
------------------	--------

CK2,5-ED-0,75BU AG - Crimp contact



1663653

<https://www.phoenixcontact.com/gb/products/1663653>

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

CK2,5-ED-0,75BU AG - Crimp contact


1663653

<https://www.phoenixcontact.com/gb/products/1663653>



Drawings

Dimensional drawing



Dimensional drawing

CK2,5-ED-0,75BU AG - Crimp contact



1663653

<https://www.phoenixcontact.com/gb/products/1663653>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1663653>



EAC

Approval ID: RU C-DE.AI30.B.01102



EAC

Approval ID: EAC-Zulassung

CK2,5-ED-0,75BU AG - Crimp contact



1663653

<https://www.phoenixcontact.com/gb/products/1663653>

Classifications

ECLASS

ECLASS-13.0	27440204
-------------	----------

ETIM

ETIM 9.0	EC000796
----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

CK2,5-ED-0,75BU AG - Crimp contact



1663653
<https://www.phoenixcontact.com/gb/products/1663653>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.015 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk