

Label - EML (100X73)R-EX - 0803259

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Label, Roll, white, unlabeled, can be labeled with: THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK X, THERMOMARK S1.1, Mounting type: Adhesive, Lettering field: 100 x 73 mm

The figure shows version

Why buy this product

- ✓ The EML...-EX self-adhesive device markers have been specifically developed for marking various types of equipment in the Ex area
- ✓ The marking requirements in terms of legibility, adhesion, and wipe resistance in potentially explosive areas (ATEX), according to IEC/EN 60079-0, can also be ensured following storage in typical gas atmospheres. Phoenix Contact developed these labels especially for process engineering, which is where these requirements typically arise.
- ✓ These labels meet the requirements for wipe resistance according to DIN EN 61010-1 against aggressive media such as acetone, ethanol, and MEK
- ✓ They are only suitable in conjunction with the TM- RIBBON110-EX
- ✓ Thanks to the special surface and adhesive, the marker meets the demanding requirements of process engineering
- ✓ A wide range of marker sizes and colors are available for custom designs
- ✓ If high-quality ink ribbons are used, the labeling is resistant to solvents and suitable for use even under harsh industrial conditions
- ✓ Precise printing quality and good adhesive properties
- ✓ The EML ... materials are UL-listed
- ✓ The special packaging protects rolls that have already been started from the dirt found in industrial environments
- ✓ The EML ... self-adhesive device markers have been specifically developed for marking various types of operating equipment in control, system, and control cabinet engineering

Key commercial data

Packing unit	1 pc
GTIN	 4 046356 939140
Weight per Piece (excluding packing)	99.99 g
Custom tariff number	39199000
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length (b)	100 mm
Width (a)	73 mm

Ambient conditions

Label - EML (100X73)R-EX - 0803259

Technical data

Ambient conditions

Ambient temperature (operation)	> -40 °C ... 150 °C
Recommended storage conditions	23 °C / 50% relative humidity. Storage in the original packaging is recommended prior to processing.

General

Color	white
Components	free from silicone and halogen
Material	Polyester
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	300
Number of individual labels per row	1
RoHS compliant	Yes
Adhesive	Acrylic
Printability	Thermal transfer
Device	5146477 THERMOMARK ROLL
Ink ribbon	0803211 TM-RIBBON 110-EX
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	Following DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result	Test passed
Foil strength	50 µm
Adhesive strength	46 µm
Marking mounting type	Adhesive

Classifications

eCl@ss

eCl@ss 5.1	27371301
eCl@ss 6.0	27371301

ETIM

ETIM 4.0	EC000761
----------	----------

Label - EML (100X73)R-EX - 0803259

Classifications

ETIM

ETIM 5.0	EC000761
----------	----------

Accessories

Accessories

Ink ribbon

Ink ribbon - TM-RIBBON 110-EX - 0803211



Ink ribbon, Length: 280000 mm, Width: 110 mm, Color: black