



**Part Number :** [732513483](#)

**Product Description :** Precision Test Connector, 27 GHz SMA PCB Jack Receptacle, 2-Hole Flange Mount, Solderless Compression Contact, with Two 6.35mm Screws, 50 Ohms

**Series Number :** 73251

**Status :** Active

**Product Category :** RF / Coaxial Connectors

---

## Documents & Resources

### Drawings

[732513483 sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[SMA CMC 73251-348x.zip](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	RF / Coaxial Connectors
Series	73251
Description	Precision Test Connector, 27 GHz SMA PCB Jack Receptacle, 2-Hole Flange Mount, Solderless Compression Contact, with Two 6.35mm Screws, 50 Ohms
Comments	Solderless Compression
Product Name	Precision Test - Optimized SMA
Style	PCB
Type	Subminiature
UPC	883906534097

### Electrical

Frequency	27 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 500 Vrms@Sea Level

### Physical

Cable Attachment	N/A
Gender	Jack
Keying to Mating Part	N/A
Net Weight	1.713/g

Orientation	Straight
Packaging Type	Tray
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	Surface Mount - Compression
PCB Thickness - Recommended	4.64mm
Reverse Polar	No
Wire/Cable Type	N/A