


## FEATURES

- **Annealed Copper Conductors:** Offers superior electrical conductivity and flexibility
- **Polyvinyl Chloride Jacket:** Provides excellent insulation and protection against environmental factors
- **5 Core Design:** Suitable for complex wiring applications
- **Temperature Range -15 °C to 90 °C:** Ensures reliable performance in diverse conditions
- **Voltage Rating of 500 V:** Suitable for medium voltage applications
- **Plain Conductor Type:** Simplifies installation and maintenance
- **24/0.2 Core Strands:** Enhances flexibility and durability
- **9.3 mm Outside Diameter:** Compact design for easy installation

## RS PRO 0.75 mm<sup>2</sup> Flexible Cable, 5 Core

RS Stock No: 606-124



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO flexible cable is designed for reliable electrical connections in various industrial applications. With a 0.75 mm<sup>2</sup> cross-sectional area and five cores, it is ideal for use in environments requiring flexible and durable cabling solutions. The cable's annealed copper conductors ensure excellent conductivity, while the PVC jacket provides robust protection.

## General Specifications

Conductor Material	Annealed Copper
Conductor Type	Plain
Jacket Colour	White
Product Type	Flexible Cable

## Mechanical Specifications

Cable CSA	0.75 mm <sup>2</sup>
Cable Length	100 m
Core Strands	24/0.2
Jacket Material	Polyvinyl Chloride
Number of Cores	5
Outside Diameter	9.3 mm

## Operation Environment Specifications

Maximum Operating Temperature	90 °C
Minimum Operating Temperature	-15 °C

## Approvals

Standards/Approvals	ACI, BASEC ISO 9001 UKAS CS1-029, BS EN 50363-3, BS EN 50363-4-1, BS EN 50525-2-11, BS EN 60228
---------------------	---

## Electrical Specifications

Voltage	500 V
---------	-------