CASM-32

Brushless DC motor BG 45 and adapters

CASM-32 linear units with brushless DC motors are perfectly suited to replace pneumatic cylinders in many applications.

It is a very simple system to set up. Connect the motor to a $24\,\mathrm{V}$ DC power supply and program up to 14 motion profiles with your computer and the programming accessory kit.


After programming the motor, the motion profile can be activated by 2-4 binary signals (PLC outputs or switches) and the actuator will run to the defined position.

The brushless, DC motor BG 45x30 PI, comes with an internal encoder with $1\,024$ counts per turn for high positioning accuracy. The internal brake is activated after each movement to secure the system in case of a power loss and to give the motor time to cool down when not in operation.

The brake also enables an increase in the power performance of a full motion cycle.

For more information, please visit the following site: www.skf.com/casm





Order numbers for a complete actuator

Order No.

Linear unit according to your needs Brushless DC motor BG 45x30 Pl Adapter kit, parallel or in-line Accessories according to your needs Cable kit for BG 45 See CASM-32 Linear units BG45X30Pl ZBE-37557x, see below See CASM-32 Accessories ZBE-530632-xx, see below

Accessories


Order No.

Programming kit for BG motor series Cable kit 3 m for BG 45 Cable kit 10 m for BG 45 Replacement belt for parallel adapter ZBE-530615 ZBE-530632-03 ZBE-530632-10 ZBE-375600-32




BLDC motor BG45 x 30

with PI interface and brake




Parallel adapter kit

for CASM-32 and BLDC motor BG 45



In-line adapter kit

for CASM-32 and BLDC motor BG 45



® SKF is a registered trademark of the SKF Group.

© SKF Group 2014

The contents of this publication are the copyright of the publisher and may not be reproduced (even extracts) unless prior written permission is granted. Every care has been taken to ensure the accuracy of the information contained in this publication but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.

PUB MT/P8 14755 EN · September 2014

Order No.:

BG45X30PI

Motor data			
	Symbol	Unit	BG 45x30 PI
Nominal torque (100 K) Stall torque (20 °C) Nominal rotational speed Nominal voltage Nominal current (100 K) Peak current (2 s) Max. output power (20 °C) Inertia with brake Weight with brake	M M ₀ ω U I I _{peak} P _{out} J	Nm Nm 1/min V DC A A kW kgm ² kg	0.25 0.942 3 360 24 4.87 15 0.159 0.0044 0.74

Order No.:

ZBE-375573



System capabilities			
	F _{peak}	F _m ¹⁾	V _{max}
CASM-32-LS CASM-32-BS CASM-32-BN	300 N 700 N 462 N	300 N 327 N 131 N	60 mm/s 150 mm/s 500 mm/s

1) Mean load over full cycle. For more information please visit skf.com/casm

Order No.:

ZBE-375570



System capabilities			
	F _{peak}	F _m 1)	V _{max}
CASM-32-LS CASM-32-BS CASM-32-BN	300 N 700 N 462 N	300 N 327 N 131 N	60 mm/s 150 mm/s 500 mm/s
1) Mean load over full cycle. For mo	ore information plea	se visit skf.com/cas	m

