

# DE1DS1A13

Empty enclosures for standard starters, TeSys LE, with 1 pushbutton and 1 knob, for LE1D09 and LE1D12



## Main

Range of product	TeSys
Range	TeSys
Device short name	DE1D
Product or component type	Enclosure
Material	Polycarbonate
Device composition	Contacteur ordered separately Thermal overload relay ordered separately
Product compatibility	LE1D12 LE1D09
Control type	Push-button reset blue R Selector switch 2 positions start/stop O-I

## Complementary

Cable entry number	2 ISO20 top 2 ISO20 bottom 2 Pg 13 bottom 2 Pg 16 bottom
Height	166 mm
Width	88 mm
Depth	165 mm
Net weight	0.3 kg

## Environment

IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 60529
Ambient air temperature for operation	-5...40 °C
Environmental characteristic	Standard environment
Product certifications	UKCA

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>