


# DATA SHEET O-Ring 106508

## PART INFORMATION

Part number	106508
Inside diameter d1	6,40 mm
Cross-section d2	1,90 mm
Size standard	R5A
Tolerance range according to	ISO 3601-1
Rubber family	NBR
Rubber compound	PC851
Quality acceptance criteria on aspect	ISO 3601-3



### PC851 COMPOUND NFORMATION

#### **Original characteristics**

Hardness Sh A Tensile strength Elongation at break Compression set TR10 Brittle point Operational temperature range \* Peak temperature

#### Rubber color

**Official agreements** Gaz : EN549 – H3B1 80 17 MPa 225 % 15 % (24h 100°C) -25 °C -35 °C -30 °C / 100 °C 120 °C

Black

## NBR FAMILY

#### **Good resistance**

Mineral oils Domestic gas Water up to 70 °C Fuels Aliphatic solvants

Poor resistance Acids Atmospheric agents Brake fluids

Particularities Good mechanical characteristics

**Typical applications** Hydraulic & pneumatic Valves & fittings water and mineral gas Mineral oil & fuel circuits

\* The temperature range is given as an indication and can be influenced by the environment, the fluids in contact and the operating conditions.



LE JOINT FRANCAIS SNC 1 rue Gutenberg ZI Ouest de Bazouges - 53200 CHATEAU-GONTIER - FRANCE www.oring.hutchinson.fr\_- oring@hutchinson.com We make it **possible**