

M12 FHAC16-502X

M12 FUEL™ COMPACT 16 MM SDS-PLUS HAMMER

Compact and balanced 12 V rotary hammer with 1.15 J of impact energy
4-mode operation: rotary hammer, hammer only, rotation only and selectable work position of the chisel (variolock) for maximum versatility

Anti-vibration system (AVS) for decreased user fatigue and lower vibration exposure. Also, an added anti-vibration side handle for lowering the vibration exposure even further

Optimised hammer drilling up to 12 mm

The DNA of our FUEL™ platform redefines the balance of cordless technologies. MILWAUKEE®'s POWERSTATE™ brushless motor, REDLITHIUM™ battery pack and REDLINK PLUS™ electronic intelligence delivering outstanding power, run time and durability

Flexible battery system: works with all MILWAUKEE® M12™ batteries



REDLITHIUM™



Blow energy [EPTA][J]	1.15
Max. percussion rate (bpm)	4,410
No load speed (rpm)	0 - 1200
Max. drilling concrete (mm)	16
Vibration drilling into concrete (m/s²)	12.3
Vibration chiseling (m/s²)	10.3
Kit included	2 x M12 HB5 Battery packs, C12 C Charger, HD Box
Article number	4933499185