

## DCD709D2T-QW

18V XR Brushless Hammer Drill Driver - 2 X 2Ah Batteries



5035048721889



### Product Description :

A powerful yet compact 18V hammer drill driver, with a length of just 175mm and a 2 speed brushless motor that delivers 65Nm of torque and extended runtime, this drill is capable of even the most demanding applications. Other features include a foot LED for better workpiece illumination and a belt hook for easy carrying when not in use.

### Product Features and Benefits :

- 18V XR Brushless Hammer Drill Driver with Compact Design
- BRUSHLESS MOTOR: Delivers high performance, extends tool life and allows for a much shorter design
- 15-POSITION ADJUSTABLE TORQUE CONTROL: For consistent screwdriving into a variety of materials
- BRIGHT LED ON TOOL FOOT: For high visibility in low light situations
- ULTRA COMPACT, LIGHTWEIGHT DESIGN: Allows use in confined spaces
- TWO SPEED ALL METAL TRANSMISSION: For increased runtime and longer tool life

### Technical specifications :

- Max. Drilling Capacity (Wood) [Metric] : 30 mm
- Max. Drilling Capacity (Masonry) [Metric] : 13 mm
- Max Torque [Metric] : 65 Nm
- Battery Capacity : 2.0 Ah
- Battery Voltage : 18 V
- Power Output : 340 W
- Max. Drilling Capacity (Metal) [Metric] : 13 mm
- Chuck Capacity [Metric] : 1.5-13 mm

### Product Warranty :

1 Year Limited Warranty, 3 Year Limited Warranty When Registered

### Product Applications :

All wood drilling tasks up to 30mm ; Screw Driving applications ; Masonry Drilling to 13mm ; Metal Drilling to 13mm

### Included items :

- Belt Hook (x1)
- TSTAK Compatible Kit Box (x1)
- 2Ah XR Battery Packs (x2)

