
DISCRETE SEMICONDUCTORS



Product specification

2003 Dec 18



30 V, 2 A PNP low V_{CEsat} (BISS) transistor

FEATURES

- Low collector-emitter saturation voltage V_{CEsat}
- High collector current capability: I_{C} and I_{CM}
- Higher efficiency leading to less heat generation
- Reduced printed-circuit board requirements
- Cost effective alternative to MOSFETs in specific applications.

APPLICATIONS

- Power management
 - DC/DC converters
 - Supply line switching
 - Battery charger
 - LCD backlighting.
- Peripheral drivers
 - Driver in low supply voltage applications (e.g. lamps and LEDs)
 - Inductive load driver (e.g. relays, buzzers and motors).

DESCRIPTION

PNP BISS transistor in a SOT23 plastic package offering ultra low V_{CEsat} and R_{CEsat} parameters.

MARKING

TYPE NUMBER	MARKING CODE ⁽¹⁾
PBSS5230T	3K*

Note

1. * = p: Made in Hong Kong.

* = t: Made in Malaysia.

* = W: Made in China.

ORDERING INFORMATION

		PACKAGE			
	NAME DESCRIPTION		VERSION		
PBSS5230T	_	plastic surface mounted package; 3 leads SOT23			

QUICK REFERENCE DATA

SYMBOL	PARAMETER	MAX.	UNIT
V _{CEO}	collector-emitter voltage	-30	V
I _C	collector current (DC)	-2	A
I _{CM}	peak collector current	-3	A
R _{CEsat}	equivalent on-resistance	220	mΩ

PINNING

PIN	DESCRIPTION	
1	base	
2	emitter	
3	collector	




Fig.1 Simplified outline (SOT23) and symbol.

PBSS5230T

30 V, 2 A PNP low V_{CEsat} (BISS) transistor

PBSS5230T

LIMITING VALUES

In accordance with the Absolute Maximum Rating System (IEC 60134).

SYMBOL	PARAMETER	PARAMETER CONDITIONS		MAX.	UNIT	
V _{CBO}	collector-base voltage	open emitter	-	-30	V	
V _{CEO}	collector-emitter voltage	open base	-	-30	V	
V _{EBO}	emitter-base voltage	open collector	-	-5	V	
I _C	collector current (DC)		_	-2	A	
I _{CM}	peak collector current	single peak	-	-3	А	
I _B	base current (DC)		-	-300	mA	
P _{tot}	total power dissipation	$T_{amb} \le 25 \ ^{\circ}C$; note 1	-	300	mW	
		$T_{amb} \le 25 \ ^{\circ}C$; note 2	-	480	mW	
Tj	junction temperature		-	150	°C	
T _{amb}	operating ambient temperature		-65	+150	°C	
T _{stg}	storage temperature		-65	+150	°C	

Notes

- 1. Device mounted on a FR4 printed-circuit board; single-sided copper; tinplated; standard footprint.
- 2. Device mounted on a FR4 printed-circuit board; single-sided copper; tinplated; mounting pad for collector 1 cm².

THERMAL CHARACTERISTICS

SYMBOL	PARAMETER	CONDITIONS	VALUE	UNIT
R _{th j-a}	thermal resistance from junction to ambient	in free air; note 1	417	K/W
		in free air; note 2	260	K/W

Notes

- 1. Device mounted on a FR4 printed-circuit board; single-sided copper; tinplated; standard footprint.
- 2. Device mounted on a FR4 printed-circuit board; single-sided copper; tinplated; mounting pad for collector 1 cm².

30 V, 2 A PNP low V_{CEsat} (BISS) transistor

PBSS5230T

CHARACTERISTICS

 $T_j = 25 \ ^{\circ}C$ unless otherwise specified.

SYMBOL	PARAMETER	CONDITIONS	MIN.	TYP.	MAX.	UNIT
I _{CBO}	collector cut-off current	$V_{CB} = -30 \text{ V}; \text{ I}_{E} = 0$	-	-	-100	nA
		$V_{CB} = -30 \text{ V}; \text{ I}_{E} = 0; \text{ T}_{j} = 150 ^{\circ}\text{C}$	-	-	-50	μA
I _{EBO}	emitter cut-off current	$V_{EB} = -4 V; I_{C} = 0$	_	-	-100	nA
h _{FE}	DC current gain	$V_{CE} = -2 \text{ V}; \text{ I}_{C} = -100 \text{ mA}$	300	450	-	
		$V_{CE} = -2 \text{ V}; I_C = -1 \text{ A}; \text{ note } 1$	200	290	-	
		$V_{CE} = -2 \text{ V}; I_{C} = -2 \text{ A}; \text{ note } 1$	100	180	-	
V _{CEsat}	collector-emitter saturation	I _C = -500 A; I _B = -50 mA	-	-70	-110	mV
	voltage	$I_{C} = -1 \text{ A}; I_{B} = -50 \text{ mA}$	—	-140	-225	mV
		$I_{\rm C} = -2$ A; $I_{\rm B} = -200$ mA	-	-240	-350	mV
R _{CEsat}	equivalent on-resistance	I _C = -500 mA; I _B = -50 mA; note 1	-	160	220	mΩ
V _{BEsat}	base-emitter saturation voltage	$I_{C} = -2 \text{ A}; I_{B} = -50 \text{ mA}; \text{ note } 1$	-	-	-1.1	V
V _{BEon}	base-emitter turn-on voltage	$V_{CE} = -2 \text{ V}; \text{ I}_{C} = -100 \text{ mA}$	-	-	-0.75	V
f _T	transition frequency	$V_{CE} = -10 \text{ V}; I_{C} = -100 \text{ mA};$ f = 100 MHz	100	200	-	MHz
C _c	collector capacitance	$V_{CB} = -10 \text{ V}; I_E = I_e = 0; f = 1 \text{ MHz}$	-	23	28	pF


Note

1. Pulse test: $t_p \leq 300 \ \mu s; \ \delta \leq 0.02.$

PBSS5230T

30 V, 2 A PNP low V_{CEsat} (BISS) transistor

PACKAGE OUTLINE



30 V, 2 A PNP low V_{CEsat} (BISS) transistor

PBSS5230T

DATA SHEET STATUS

LEVEL	DATA SHEET STATUS ⁽¹⁾	PRODUCT STATUS ⁽²⁾⁽³⁾	DEFINITION
I	Objective data	Development	This data sheet contains data from the objective specification for product development. Philips Semiconductors reserves the right to change the specification in any manner without notice.
11	Preliminary data	Qualification	This data sheet contains data from the preliminary specification. Supplementary data will be published at a later date. Philips Semiconductors reserves the right to change the specification without notice, in order to improve the design and supply the best possible product.
	Product data	Production	This data sheet contains data from the product specification. Philips Semiconductors reserves the right to make changes at any time in order to improve the design, manufacturing and supply. Relevant changes will be communicated via a Customer Product/Process Change Notification (CPCN).

Notes

- 1. Please consult the most recently issued data sheet before initiating or completing a design.
- 2. The product status of the device(s) described in this data sheet may have changed since this data sheet was published. The latest information is available on the Internet at URL http://www.semiconductors.philips.com.
- 3. For data sheets describing multiple type numbers, the highest-level product status determines the data sheet status.

DEFINITIONS

Short-form specification — The data in a short-form specification is extracted from a full data sheet with the same type number and title. For detailed information see the relevant data sheet or data handbook.

Limiting values definition — Limiting values given are in accordance with the Absolute Maximum Rating System (IEC 60134). Stress above one or more of the limiting values may cause permanent damage to the device. These are stress ratings only and operation of the device at these or at any other conditions above those given in the Characteristics sections of the specification is not implied. Exposure to limiting values for extended periods may affect device reliability.

Application information — Applications that are described herein for any of these products are for illustrative purposes only. Philips Semiconductors make no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

DISCLAIMERS

Life support applications — These products are not designed for use in life support appliances, devices, or systems where malfunction of these products can reasonably be expected to result in personal injury. Philips Semiconductors customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Philips Semiconductors for any damages resulting from such application.

Right to make changes — Philips Semiconductors reserves the right to make changes in the products including circuits, standard cells, and/or software described or contained herein in order to improve design and/or performance. When the product is in full production (status 'Production'), relevant changes will be communicated via a Customer Product/Process Change Notification (CPCN). Philips Semiconductors assumes no responsibility or liability for the use of any of these products, conveys no licence or title under any patent, copyright, or mask work right to these products, and makes no representations or warranties that these products are free from patent, copyright, or mask work right infringement, unless otherwise specified.

Philips Semiconductors – a worldwide company

Contact information

For additional information please visit http://www.semiconductors.philips.com. Fax: +31 40 27 24825 For sales offices addresses send e-mail to: sales.addresses@www.semiconductors.philips.com.

© Koninklijke Philips Electronics N.V. 2003

All rights are reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner.

The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Printed in The Netherlands

R75/01/pp7

Date of release: 2003 Dec 18

Document order number: 9397 750 11903

SCA75

Let's make things better.





Philips Semiconductors