



Relays & Contactors > Electromechanical Relays



Relay & Contactor Type: **General Purpose Power Relay**

Current Type: **DC**

Coil Magnetic System: **Polarized, Monostable**

Contact Arrangement: **1 Form C SPDT-CO**

Contact Current Rating: **25 A**

Features

Product Type Features

Relay & Contactor Type	General Purpose Power Relay
------------------------	-----------------------------

Configuration Features

Contact Arrangement	1 Form C SPDT-CO
---------------------	------------------

Electrical Characteristics

Coil Resistance	320 Ω
Contact Current Rating	25 A
Coil Voltage Rating	28 VDC

Body Features

Enclosure Type	Hermetically Sealed
----------------	---------------------

Contact Features

Contact Material	Silver Cadmium Oxide
Terminal Plating	Tin-Lead

Termination Features

Main Termination & Connection Type	Solder Pins
Coil Termination & Connection Type	Solder Pins

Mechanical Attachment

Product Mounting Feature Type	Mounting Brackets
-------------------------------	-------------------



Product Mount Type	Panel & Printed Circuit Board
--------------------	-------------------------------

Usage Conditions

Operating Temperature Range	-70 – 125 °C[-94 – 257 °F]
Environmental Ambient Temperature (Max)	125 °C[257 °F]

Operation/Application

Vibration Resistance	30G's, 10 – 3000Hz
Shock Resistance	200G's, 6ms
Current Type	DC
Coil Magnetic System	Polarized, Monostable

Product Compliance

For compliance documentation, visit the product page on TE.com>





EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Cd (10% in Component Part) Cadmium oxide (3% in Component Part) Article Safe Usage Statements: Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not lead free process capable

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 7-1617806-3 FCAC-325-BX3=RELAY, 3PST W/AUX	 TE Part # 6-1617753-4 FCA-325-CY3	 TE Part # 1-1617815-1 FCAC-150-CY4=50 AMP MID RANGE AUX RELAY	 TE Part # 8-1617806-8 FCAC-325-CX4=RELAY, 3PST W/AUX
 TE Part # 5-1617753-0 FCA-325-BZ4	 TE Part # 6-1617806-8 FCAC-325-AV8=RELAY, 3PST W/AUX	 TE Part # 9-1617815-6 FCAC-325-AV6=RELAY, 3PST W/AUX	 TE Part # 3-1617753-7 FCA-325-AY2
 TE Part # 5-1617814-4 FCA-325-BZ9	 TE Part # 1-1617795-0 FCA-150-BY4=Relay	 TE Part # 4-1617813-3 FCA-325-AZ3	 TE Part # 2-1617801-4 FCAC-150-KR3=50 AMP W/AUX RELAY
 TE Part # 4-1617753-5 FCA-325-BY2	 TE Part # 9-1617805-3 FCA-150-KX4=50 AMP 1PST/NO DM RELAY		

Also in the Series | CII FCA-125 Series



AC Relays(10)

General Purpose Power Relays(78)

PCB Relays(22)

Plug-In Relays(25)

Customers Also Bought

TE Part #1-1879447-0
TE 200W 5R6 5% Bracket

TE Part #CAT-P592-R472A
PIDG Ring Tongue Terminals

TE Part #1-321897-3
DG 22-16 HT ALUMEL R 8

TE Part #CB83444003
RW-200-E-5/8-0-SP

TE Part #NB15734001
RNF-150-1/8-0-SP

TE Part #342183-1
12-10 F.E.P.G. RING TONGUE 3BA

TE Part #5-1617753-0
FCA-325-BZ4

TE Part #046933-000
462W023-25-0

TE Part #3-2176459-6
SMW 7W 3R0 5% Taped

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_4-1617748-6_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_4-1617748-6_B.3d_igs.zip



English

Customer View Model

[ENG_CVM_CVM_4-1617748-6_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[5-1773450-5_sec5_FCA-125](#)

English

RELAY

English