

# LG7K06V708

Enclosed DOL starter, TeSys LG, 2.5-4A, 400V  
AC coil, including 1 LC1K, GV2ME with  
emergency stop, 2 pushbuttons

## Main

Range	TeSys
Product name	TeSys LG
Device short name	LG7K
Product or component type	Enclosed DOL starter
Device application	Safety
Utilisation category	AC-3
Device composition	Contactors Circuit-breaker
Motor power kW	0.75 kW at 220/230 V AC 50/60 Hz 1.5 kW at 400/415 V AC 50/60 Hz 1.5 kW at 440 V AC 50/60 Hz
Thermal protection adjustment range	2.5...4 A
[Uc] control circuit voltage	400 V AC 50/60 Hz
Control type	Push-button start white I Push-button stop black O Mushroom head push-button emergency stop red

## Complementary


Standards	IEC 60947-4-1 IEC 60204-1
Product certifications	CE[RETURN]UKCA
Cable entry number	4 2 Pg 13 + 2 Pg 16 top 4 2 Pg 13 + 2 Pg 16 bottom
Height	165 mm
Depth	177 mm
Net weight	1.3 kg
Width	175 mm

## Environment

Material	Polycarbonate
IK degree of protection	IK07 conforming to IEC 60529
IP degree of protection	IP55 conforming to IEC 60529
Environmental characteristic	Standard environment

## Offer Sustainability

Packaging without single use plastic	Yes
Packaging made with recycled cardboard	No
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>

Circularity Profile	<a href="#"> End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Take-back	No
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	107