

**BOSCH**

Invented for life

# Product data sheet

## Power tools for trade & industry

Angle Grinder

### PRO GWS 22-230 P



Robust design, solid performance – with PROtection switch for increased user protection

#### The most important data

Rated input power	2,200 W
No-load speed	6,500 rpm
Disc diameter	230 mm

**Part Number** 0 601 8C1 170

## Technical data

### Technical data

Rated input power	2,200 W
No-load speed	6,500 rpm
Grinding spindle thread	M14
Disc diameter	230 mm
Rubber backing pad, diameter	230 mm
Wire cup brush, diameter	100 mm
Weight	5.5 kg
Switch	PROtection Switch
Packaging dimensions (width x length x height)	190 x 574 x 118 mm
Voltage, electrical	230 V

## Noise/vibration information

### Surface grinding (roughing)

Vibration emission value ah	5.5 m/s <sup>2</sup>
Uncertainty K	1.5 m/s <sup>2</sup>

### Sanding with sanding sheet

Vibration emission value ah	2.5 m/s <sup>2</sup>
Uncertainty K	1.5 m/s <sup>2</sup>



# Product data sheet

Power tools for trade & industry

---

## Advantages:

- High material removal rate of new 2,200-W motor ensures strong cutting results
- Lower heating of overall motor system and improved contact between motor and carbon brushes for longer lifetime
- PROtection switch for enhanced user protection

**HEAVY  
DUTY**

---

You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

