



MODEL NAME : 2512 REV. A

FRONT VIEW



Pin#	Assignment
1	UR
2	LR
3	S
4	UL
5	LL

5 Pin 2.54mm Pitch Female Connector



NOTES:

1. ITO GLASS THICKNESS : 2.80mm
2. OVERALL THICKNESS : 3.30±0.30mm
3. CONNECTOR AND PINOUT AS INDICATED
4. FRONT SURFACE : ANTI-GLARE HARDCOAT
5. LAYER TO LAYER ASSEMBLY TOLERANCE: ±0.50mm
6. TAIL TYPE : IMMERSION GOLD PLATED FPC WITH AMP-C TIN PLATED CONTACTS
7. OTHER SPEC : SEE APPROVAL SHEET



REVISION			
NO.	DATE	DESCRIPTION	CHK
A	MAR.06.07	Pattern modified	Alex
CHIEF OF DESIGN	APPROVED	Alex	
ENGINEER	PROJECT MANAGER		
DRAWN BY	WILLIAM	DATE	MAR. 06,2007
SHT	1	OF	1
REV.			

Apex Material Technology Corp.

TOLERANCES UNLESS SPECIFIED		MODEL NAME : 2512
.X	± 0.50	DWG No : 2512-1-01
.XX	± 0.50	SCALE: 1:1 UNIT: mm
.XXX	± 0.30	
ANGULAR	.	