

Rittal – The System.

Faster – better – everywhere.

► Wall-mounted cooling unit Blue e+ Total cooling output 2.00 – 6.00 kW – SK 3187.630

Date : Sep 4, 2019

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Wall-mounted cooling unit Blue e+ Total cooling output 2.00 – 6.00 kW – SK 3187.630

created: 04.09.2019 build on www.rittal.com/uk-en



Product description

Benefits: Average 75% energy savings thanks to speed-regulated components and heat pipe technology
Suitable for international use due to a unique multi-voltage capability
Longer service life of the components inside the enclosure and the cooling unit due to component-friendly cooling
Intuitive operation due to touch display and intelligent interfaces

Material: Stainless steel 1.4301 (AISI 304)

Colour: RAL 9007

Protection category IP to IEC 60 529: Internal circuit IP 55

Supply includes: Nano-coated condenser
Integral electric condensate evaporation
Assembly parts
Fully wired ready for connection (plug-in terminal strip)

Note: Please observe the mounting instructions.
Firmware can be updated using the RiDiag III software (3159.300)

Options: For remote monitoring and networking of cooling units and chillers in the Blue e+ generation, please use the IoT interface (Model No. 3124.300). Increase machine availability and process reliability with remote monitoring of device data, statuses and system messages.

Product features

Variant: wall-mounted

Total cooling output to DIN EN 14511:	L 35 L 35 at 50 Hz: 2.6 kW L 35 L 35 at 60 Hz: 2.6 kW L 35 L 50 at 50 Hz: 1.82 kW L 35 L 50 at 60 Hz: 1.82 kW
Air throughput (unimpeded air flow):	External circuit: 1250 m ³ /h Internal circuit: 1250 m ³ /h
Rated operating voltage:	110 V - 240 V, 1~, 50 Hz/60 Hz 380 V - 480 V, 3~, 50 Hz/60 Hz
Dimensions:	Width: 450 mm Height: 1600 mm Depth: 294 mm
Temperature control:	e+ controller (factory setting +35 °C)
Temperature range:	Bearing: -40 °C...+70 °C Operation (environment): -20 °C...+60 °C Setting range: +20 °C...+50 °C
Refrigerant/cooling medium:	Refrigerant: R134a Quantity: 1150 g CO ₂ equivalent (CO _{2e}): 1.64 t
Power consumption P_{el}:	L 35 L 35 at 50 Hz: 0.99 kW L 35 L 35 at 60 Hz: 0.99 kW L 35 L 50 at 50 Hz: 0.94 kW L 35 L 50 at 60 Hz: 0.94 kW
Seasonal energy efficiency ratio (SEER) 50/60 Hz:	6.2
Packs of:	1 pc(s).
Weight/pack:	54.8 kg
EAN:	4028177934672
Customs tariff number:	84158200
ETIM 6.0:	EC000855
ETIM 5.0:	EC000855
eCl@ss 8.0/8.1:	27180704
eCl@ss 7.0/7.1:	27180704
eCl@ss 6.0/6.1:	27180704

Approvals

Approvals: Approval overview UL + C-UL

Certificates: EAC

Declarations: Declaration of conformity
Declaration of conformity - F-gas regulation