

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Emalytics Controller demo license for test and engineering purposes with unlimited functionality and 12-month validity, which will be renewed annually.

**This license is not approved for use in production systems.**

**Licenses for use in production systems are available separately.**

Please note: By using the demo license, the controller used will be bound to the demo license for the long term. Productive operation is no longer possible for a controller licensed for demo purposes. That is why we recommend using a dedicated controller for internal testing purposes.

## Commercial data

Item number	1061902
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	DRH
Product key	DRHBAA
GTIN	4055626717036
Weight per piece (including packing)	0.01 g
Weight per piece (excluding packing)	0.01 g
Customs tariff number	49111010
Country of origin	US

## Technical data

### Notes

Note on application	This license is not approved for use in production systems. Licenses for use in production systems are available separately.
Note on application	By using the demo license, the controller used will be bound to the demo license for the long term. Productive operation is no longer possible for a controller licensed for demo purposes. That is why we recommend using a dedicated controller for internal testing purposes.

### Product properties

Product type	Building management system
Area of application	Building technology

### System properties

Type of software	Embedded
Intended use for the software	Automation Engineering

### License information

Type of license	Demo license
License duration	nicht relevant

### Functionality

Integrated function	Analysis
	Data acquisition
	Diagnostics
	Startup
	Communication
	Configuration
	Project planning
	Simulation
Target system	Automation station
Supported controllers	ILC 2050 BI
Number of data points	not relevant
Number of clients	nicht relevant

### System requirements

Languages supported	German, English
Screen resolution	1024 x 768 pixel(s) ,or higher

# NC4-DEMO - Building management system



1061902

<https://www.phoenixcontact.com/in/products/1061902>

## Classifications

### ECLASS

ECLASS-11.0	27242590
ECLASS-12.0	27242590
ECLASS-13.0	27242590

### ETIM

ETIM 9.0	EC001435
----------	----------

### UNSPSC

UNSPSC 21.0	43233600
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

# NC4-DEMO - Building management system



1061902

<https://www.phoenixcontact.com/in/products/1061902>

## Accessories

### ILC 2050 BI - Controller

2403160

<https://www.phoenixcontact.com/in/products/2403160>



Modular Inline controller for automation applications in the fields of building technology, infrastructure, and energy technology. Equipped with two logically separated IP address interfaces each with 2 integrated Fast Ethernet ports. Configurable assignment of the Ethernet ports for the use of the spanning-tree protocol, daisy chain and redundant ring structures for maximum availability. Four LAN, two USB, and two RS-485 interfaces are integrated. The data point connections can be extended with up to 63 Inline I/O modules: digital and analog, function terminals for DALI, pulse counting, MBUS or serial interfaces.

---

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.  
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420  
[info@phoenixcontact.co.in](mailto:info@phoenixcontact.co.in)