




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.82 – 3.31 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Insertion Force	Normal
-----------------	--------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Flag
Contact Base Material	Phosphor Bronze
Terminal Plating Material	Tin
Crimp Type	Tab-Lok
Barrel Type	Open

Termination Features

--	--

Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple

Dimensions

Product Length	17.02 mm[.67 in]
Compatible Insulation Diameter Range	2.79 – 5.33 mm[.11 – .21 in]
Terminal Material Thickness	.46 mm[.018 in]
Wire Size	.82 – 3.31 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
---	---------

Packaging Features

Packaging Quantity	4000
Packaging Method	Strip/Reel

Other

Line	Premier
------	---------

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2232111-2 250 FASTON,FLAG,REC.,12-20 AWG, BR	 TE Part # 1855041-1 HINDGE BAR F.A. EMPO160TAB1800 LM & G	 TE Part # 61187-1 250 FASTON FLAG REC 12-10 AWG PHBZ	 TE Part # 62056-7 250 FASTON FLAG REC 18-12 AWG TPBZ
 TE Part # 60274-2 250 FASTON FLAG REC 18-12 AWG TPBZ	 TE Part # 1596696-2 HB APPL,AOL	 TE Part # 62056-6 250 FASTON FLAG REC 18-12 AWG TPBZ	 TE Part # 1852633-1 EAPOHB160TABLOCK1800 LM/G-HINGE BAR
 TE Part # 2232111-3 250 FASTON,FLAG,REC.,12-20 AWG, TPBR	 TE Part # 62056-2 250 FASTON FLAG REC 18-12 AWG SPBZ	 TE Part # 2232111-1 250 FASTON,FLAG,REC.,12-20 AWG, TPBR	 TE Part # 63137-1 250 FASOTN FLAG REC 20-16 AWG TPBZ



TE Part # 61188-1
250 FASTON FLAG REC 16-12 AWG
TPBZ



TE Part # 1596697-5
HB APPL,AOM



TE Part # 7-1855041-7
SPARE PART KIT




TE Part # 2088156-2
MINI APPLICATOR, HINGE BAR END
FEED

Also in the Series | FASTON 250



Compression Connectors(4)




Crimp Terminal Housings(116)



Insertion & Extraction Tools(6)



Insulation Boots & Sleeves(16)



Magnet Wire Terminals(1)



PCB Terminals(133)




Quick Disconnects(421)



Splices(4)

Customers Also Bought




TE Part #41996
SPLICE 7400-10000 CMA TPBR




TE Part #1-454276-1
FLOATING SHEAR



TE Part #141352-4
110 FASTON,FLAG,REC.,22-18 AWG,
PTBR




TE Part #350201-2
.140 DIA PIN 14-10 PTPPHBZ




TE Part #2238017-1
VAL-U-LOK SKT BR SN 18-22AWG



TE Part #2-1649328-2
RTD34012



TE Part #350200-2
.140 DIA SOK 14-10 PTPPHBZ



TE Part #2029112-3
3P RCPT SR VAL-U-LOK GW



Documents

Product Drawings

250 FASTON FLAG REC 18-12 AWG TPBZ

English

CAD Files

Customer View Model

ENG_CVM_CVM_41800_AP.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_41800_AP.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_41800_AP.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

82004 FASTON Terminals (Insulated and Uninsulated) Catalog - FASTON Receptacles Section

English

1654742_HOUSEHOLD_APPLIANCES_RAST5

English

Product Specifications

Engineering Report

English

Agency Approvals

Agency Approval Document

English