




Wire & Cable > Wire & Cable Accessories > Cable Ties



Cable Tie Style: **Standard**

Packaging Method: **Bag/Box**

Tensile Strength: **550 Newton**

Product Length: **750 mm [29.6 in]**

Features

Product Type Features

Cable Tie Style	Standard
Tensile Strength	550 Newton

Body Features

Primary Product Color	Black
Primary Product Material	Polyamide 6.6 GF

Dimensions

Compatible Cable Bundle Diameter Range	200 mm[7.87 in]
Product Length	750 mm[29.6 in]
Product Width	7.8 mm[.307 in]
Product Thickness	2.07 mm[.081 in]

Packaging Features

Packaging Method	Bag/Box
Packaging Quantity	100

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2025 (247)
Candidate List Declared Against: JAN 2025 (247)
Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # EC6492-000
[13611438](#)



TE Part # EC6457-000
[13611403](#)



TE Part # EC6454-000
[13611400](#)



TE Part # EC6459-000
[13611405](#)



TE Part # EC6472-000
[13611418](#)



TE Part # EC6479-000
[13611425](#)



TE Part # EC6485-000
[13611431](#)




TE Part # EC6526-000
[13611907](#)



 TE Part # EC6546-000 13611927	 TE Part # EC6552-000 13611933	 TE Part # EC6406-000 13611101	 TE Part # EC6475-000 13611421
 TE Part # EC6481-000 13611427	 TE Part # EC6494-000 13611440	 TE Part # EC6523-000 13611904	 TE Part # EC6534-000 13611915
 TE Part # EC6541-000 13611922	 TE Part # EC6471-000 13611417	 TE Part # EC6543-000 13611924	 TE Part # EC6550-000 13611931

Customers Also Bought

 TE Part #CAT-AM71-CH8172 AMP SUPERSEAL 1.5MM, CONNECTOR HOUSING	 TE Part #281934-2 SINGLE WIRE SEAL	 TE Part #CAT-D48-ST273 DEUTSCH Solid Contacts	 TE Part #206070-8 CABLE CLAMP KIT #17
 TE Part #DT04-2P REC, 2P, GRY, N	 TE Part #DT06-2S PLG, 2P, GRY, N	 TE Part #CAT-D487-W416 Wedgelocks: DEUTSCH DT	

Documents



Product Drawings

CABLE TY 750X7,8BLA

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-160986-2_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-160986-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-160986-2_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

CABLE TIES

English