



Terminals & Splices > Magnet Wire Terminals



Magnet Wire Terminal Type: **Multispring Pin**
Mating Pin Diameter: **.8 mm [.031 in]**
Magnet Wire Size: **.63 – .85 mm**
Termination Method to Wire & Cable: **Insulation Displacement (IDC)**

Features

Product Type Features

Compatible With Discrete Wire Type	Magnet Wire, Solid
------------------------------------	--------------------

Contact Features

Magnet Wire Terminal Type	Multispring Pin
Mating Pin Diameter	.8 mm[.031 in]
Terminal Plating Material	Tin
Contact Underplating Material	Nickel
Terminal Orientation	Straight

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Dimensions

Terminal Height	7.6 mm[.3 in]
Magnet Wire Size	.63 – .85 mm
Stock Thickness (Magnet Wire Side)	.32 mm[.013 in]
Product Length	14.8 mm[.582 in]



Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-65 – 150 °C[-85 – 302 °F]

Operation/Application

Compatible With Wire Base Material	Aluminum
------------------------------------	----------

Identification Marking

Identification Number	12
-----------------------	----

Packaging Features

Packaging Method	Reel, Reel/Carton
------------------	-------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1247001-2
MAGMATE "300 SERIES" WITH
MULTISPRING PIN

TE Part # 1247001-3
MAGMATE "300 SERIES" WITH
MULTISPRING

TE Part # 1247004-2
MAGMATE "300 SERIES" WITH
MULTISPRING PIN

TE Part # 1247002-2
MAGMATE "300 SERIES" WITH
MULTISPRING PIN

TE Part # 1247002-3
MAGMATE "300 SERIES" WITH
MULTISPRING

TE Part # 2238145-2
MAGMATE 300 SERIES WITH
MULTISPRING PIN

TE Part # 2238145-3
MAGMATE 300 SERIES WITH
MULTISPRING PIN

TE Part # 1247003-2
MAGMATE "300 SERIES" W/H
MULTISPRING PIN

TE Part # 1247000-2
MAGMATE "300 SERIES" WITH
MULTISPRING PIN

TE Part # 1247004-3
MAGMATE "300 SERIES" WITH
MULTISPRING

Also in the Series | **MAG-MATE 300**

Magnet Wire Terminals(77)

Customers Also Bought


TE Part #42282-1
FF 250 REC 18-14AWG BR LP

TE Part #1-84953-0
1MM FPC HORZ.TOP CONT.ASSY 10P

TE Part #1-103638-5
16 MTE HDR SRST LATCH .100CL

TE Part #2-180930-5
250 FASTON HSG.,REC.,1 POS,BLACK





TE Part #3-350819-2
ULTRA-FAST 250 ASY REC 16-14 AWG
TPBR



TE Part #1393249-7
W58-XB1A4A-10=W58



TE Part #1879075-3
THS25 R05 5%



TE Part #3-2176057-5
RLP73K 3A R27 1% 1K RL



TE Part #1-2176331-4
CRGP 2512 120R 1%

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1247003-3_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1247003-3_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1247003-3_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English