



Product data sheet

Power tools for trade & industry

Cordless Drill/Driver

GSR 18V-150 C



When strength counts – the clever drill driver for unrivalled power and control

The most important data

Max. screw diameter	13 mm
Weight excl. battery	2.1 kg
Torque (soft/hard/max.)	84/100/150 Nm

Part Number 0 601 9J5 002

[> More product information](#)

Technical data

Technical data

Torque (soft/hard/max.)	84/100/150 Nm
No-load speed (1st gear / 2nd gear)	0 – 550 / 0 – 2,200 rpm
Battery type	Lithium-ion
Chuck capacity, min./max.	1.5 / 13 mm
Weight excl. battery	2.1 kg
Torque settings	25+1

'Total vibration values (Drilling in metal)'

Vibration emission value ah	2.5 m/s ²
Uncertainty K	1.5 m/s ²

Drilling diameter

Max. drilling diameter in wood	150 mm
Max. drilling diameter in steel	16 mm

Screw diameter

Max. screw diameter	13 mm
---------------------	-------

Noise/vibration information

Drilling in metal

Vibration emission value ah	2.5 m/s ²
Uncertainty K	1.5 m/s ²

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Enormously fast work progress due to ProCORE18V batteries and a powerful brushless motor with a maximum torque of 150 Nm
- Unmatched control at every step due to precise Electronic Angle Detection and switchable KickBack Control
- Metal drill chuck and metal gearbox for more reliability and robustness

