



Connectors > Contacts > Connector Contacts



Contact Type: **Socket**

Contact Mating Area Plating Material: **Gold (Au)**

Compatible With Wire & Cable Type: **FFC**

Termination Method to Wire & Cable: **Insulation Displacement (IDC)**

Contact Base Material: **Phosphor Bronze**

Features

Configuration Features

Compatible With Wire & Cable Type	FFC
-----------------------------------	-----

Contact Features

Contact Underplating Material	Palladium Nickel
	15 µin
Contact Type	Socket
Contact Mating Area Plating Material	Gold (Au)
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	2 A

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
Product Terminates To	Wire & Cable

Dimensions

Accepts Conductor Width	1.27 mm, 1.62 mm
-------------------------	------------------

Usage Conditions

Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]
-----------------------------	----------------------------



Operation/Application

Circuit Application	Signal
---------------------	--------

Packaging Features

Packaging Method	Reel
------------------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 88117-9
FFC PIN CONT 15AU RL

TE Part # 4-528441-9
APPL.FFC-CARD EDGE

TE Part # 1-528013-1
FFC PISTOL GRIP HAND TOOL CASE

Customers Also Bought

TE Part #953382-1
COVER FOR 6W HSG MQS GEN2

TE Part #CAT-M5833-F3492A
Female-on-Board Connector, Top Entry

TE Part #328394
PIDG SPD 22-16COMM 22-18MIL 2

TE Part #CAT-SIGH262
Signal Header

TE Part #4-176891-4
1.25FP,P14,DL,O,N,TR,5.00,6.90

TE Part #2071583-2
ECK100BH5AAA

TE Part #2-963964-4
MQS STIFTE MAGAZ

TE Part #2295018-2
SPLASH PROOF USB TYPE C REC, DUAL SMT

Documents

Product Drawings

FFC,CARD EDGE CONTACT

English

CAD Files

Customer View Model

ENG_CVM_CVM_485800-5_AK.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_485800-5_AK.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_485800-5_AK.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

485800-5

Socket Contact, Gold (Au), FFC, Insulation Displacement (IDC), Phosphor Bronze,
Signal, -65 – 105 °C [-85 – 221 °F]



Product Specifications

Application Specification

English