
KEMET Part Number: C0805C470J5GACTU

(C0805C470J5GAC7800)



SMD Comm COG, Ceramic, 47 pF, 5%, 50 VDC, COG, SMD, MLCC, Ultra-Stable, Low Loss, Class I, 0805



Dimensions	
L	2mm +/-0.2mm
W	1.25mm +/-0.2mm
Т	0.78mm +/-0.10mm
S	0.75mm MIN
В	0.5mm +/-0.25mm

Packaging Specifications		
Packaging:	T&R, 180mm, Paper Tape	
Packaging Quantity:	4000	

General Information		
Supplier:	KEMET	
Series:	SMD Comm C0G	
Style:	SMD Chip	
Description:	SMD, MLCC, Ultra-Stable, Low Loss, Class I	
Features:	Ultra-Stable, Low Loss, Class I	
RoHS:	Yes	
Termination:	Tin	
Marking:	No	
Miscellaneous:	Note: KEMET 50V rated parts may be operated at 63 Volts	
Chip Size:	0805	
Shelf Life:	78 Weeks	
MSL:	1	

Specifications	
Capacitance:	47 pF
Capacitance Tolerance:	5%
Voltage DC:	50 VDC
Dielectric Withstanding Voltage:	125 VDC
Temperature Range:	-55/+125C
Temperature Coefficient:	COG
Dissipation Factor:	0.10% 1MHz 25C
Aging Rate:	0% Loss/Decade Hour
Insulation Resistance:	100 GOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

