

**Part Number :** [734151121](#)

**Product Description :** MMCX Plug, Right-Angle, Crimp, RG-174, RG-188 and RG-316 Cable, Brass Body, Gold (Au) Plated, Bag, 50 Ohms

**Series Number :** 73414

**Status :** Active

**Product Category :** RF / Coaxial Connectors



## Documents & Resources

### Drawings

[734151121\\_sd.pdf](#)

### 3D Models and Design Files

[734151121\\_stp.zip](#)

### Specifications

[896755070-000.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant with Exemption 3; 34; 33
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	RF / Coaxial Connectors
Series	73414
Description	MMCX Plug, Right-Angle, Crimp, RG-174, RG-188 and RG-316 Cable, Brass Body, Gold (Au) Plated, Bag, 50 Ohms
Product Name	MMCX
Style	Cable
Type	Microminiature
UPC	800755959598

### Electrical

Frequency	6 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 170 Vrms@Sea Level

### Physical

Cable Attachment	Crimp
Gender	Plug
Keying to Mating Part	N/A
Net Weight	0.768/g
Orientation	Right Angle
Packaging Type	Bag
Panel Mount	No

Panel Mount Method	N/A
PCB Mounting	N/A
Reverse Polar	No
Wire/Cable Type	LMR-100, RG-174, RG-188, RG-316

### **Solder Process Data**

Lead-Free Process Capability	N/A
------------------------------	-----

---

This document was generated on Jul 09, 2025