

PRODUCT-DETAILS

22R086

RING TERM CU 16-12 AWG NO8 STUD



General Information

Extended Product Type	22R086
Product ID	7TAI029030R0025
EAN	5414363112129
Catalog Description	RING TERM CU 16-12 AWG NO8 STUD
Long Description	Insulation Piercing Magnet Wire Ring Terminal, Length .91 Inches, Width .30 Inches, Length of Teeth .45 Inches, Width of Teeth .25 Inches, Stud Size 8, Wire Range #16 AWG - #12 AWG 2,580 Circular Mil Area - 12,330 Circular Mil Area, Copper Alloy, Tin Plated

Ordering

EAN	5414363112129
UPC	786210889986

Dimensions

Product Net Length	0, mm
--------------------	-------

Container Information

Package Level 1 Units	1000 piece
Package Level 1 Width	4.5 in 114 mm
Package Level 1 Height	3 in

	76 mm
Package Level 1 Depth / Length	6 in 152 mm
Package Level 2 Units	5000 piece
Package Level 2 Width	8.8 in 224 mm
Package Level 2 Height	7.5 in 191 mm
Package Level 2 Depth / Length	10.4 in 264 mm

Additional Information

Application	For aluminum to copper, aluminum to aluminum or copper to copper magnet wire connections.
Brand / Label	Sta-Kon
Effective Date	19761122
Material	Copper
Number of Batteries	0
Product Name	STA-KON AND CATAMOUNT TERMINAL
Product Type	Ring Terminal
Special Functions	Designed to penetrate magnet wire insulation during application, eliminating the need for stripping, brazing, welding or other methods of joining magnet wire.
Standards	UL E9809

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	22R086
Instructions and Manuals	22R086

Classifications

ETIM 6	EC001052 - Solderless copper terminals for copper conductors
ETIM 7	EC001052 - Solderless copper terminals for copper conductors
UNSPSC	39121432
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4603 >> Electrical terminals

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Compression & Mechanical Connectors

