


Technical data

NA4852

Needle roller bearing, machined-ring, with inner ring



Needle roller bearing, machined-rings, with inner ring, double-side ribs

VISUAL (S)



PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	260 mm
D - External diameter	320 mm
C - Width of bearing, drawn cup or outer ring	60 mm
F - Under roller diameter	285 mm
rs - Min fillet radius	2 mm
s - Max axial offset	2 mm
Lubrication hole on outer ring	Oui/Yes

PRODUCT DEFINITION

k - Hole diameter	4 mm
Lubrication hole on inner ring	Non/No
Radial clearance class	CN
Precision class	P0
Mass	10,8 kg

PRODUCT PERFORMANCE

Cr - Dynamic load rating	375 kN
C0r - Static load rating	1160 kN
N lim - Grease lubrication limit speed	950 tr/min
N lim - Oil lubrication limit speed	1400 tr/min
Tmin - Min operating temperature	-20 °C
Tmax - Max operating temperature	120 °C

ABUTMENT

da min - Min shoulder diameter IR	269 mm
Da max - Max shoulder diameter OR	311 mm
ras max - Max shaft & housing fillet radius	2 mm

ESHOPDONOTDISPLAY

Tracepart	Oui/Yes
Reference	NA4852
Image	NRBNA59_1.jpg, NRBNA59_3.jpg
Rolling element material	Acier 100Cr6

