



FAX-T104
The compact, stylish
fax with integral phone.



Telephone



www.brother.com

••• always at your side

A small, stylish machine with advanced business functions as standard, plus an integral telephone.

With an integral handset, easy to operate numerical keypad and clearly labelled functions, the FAX-T104 offers a professional solution to your telephone and fax needs. In telephone mode users have the benefit of an on-hook dialling facility in addition to a background melody whilst callers are on hold.

The FAX-T104 has been built with efficiency at the forefront of its design. Your most common fax destinations can be stored in one-touch dial facility and there is speed dialling for up to 100 names via simple navigation dial keys.

Accepting up to 30 sheets of standard A4 paper together with the advantage to store up to 25 pages[†] of memory ensures vital fax messages are never missed.



The automatic document feeder accepts up to 10 sheets, enabling you to send and copy multi-page documents.

FAX-T104 is both quick and easy to select any of the advanced business features – including the ability to send the same fax message to a number of recipients simultaneously, saving time and effort.

It also offers a number of useful copy functions such as the ability to automatically sort multiple copies, as well as the option to reduce or enlarge documents from 50-150%.

All the professional quality you expect built into a compact and stylish machine that is ideal for the small office or home

[†] ITU-T-Test Chart No. 1, Out of Paper Reception, ECM Mode.

Technical Specifications

General

Plain paper thermal transfer fax
10 sheet auto document feeder (ADF)
30 sheet paper capacity
Up to 25 pages out of paper reception[†]
LCD display of 16 characters on 1 line
On screen programming – prompts displayed within the LCD
Automatic recognition of fax & telephone reception

Telephone

Integrated telephone handset
Integrated speaker for 'On-Hook Dialling'
On hold background music
4 one-touch dials
100 speed dials

Fax

9,600 bps Modem
15 second transmission speed
Group 3 ITU-T group compatibility
Automatic redial
Transmission lock to prevent unauthorised access and transmission or reception of faxes
Caller ID*, allows you to see the name or number of the caller (available for SPA/ GER/ FRA/ AUS/ UK/ IRE/ NOR/ SWE/ DEN/ BEL/ POR/ ITA/ HOL)
ECM, Error Correction Mode will automatically detect errors during transmission and resend relevant pages. (Where both machines share ECM feature)
Transmission verification report
Super fine transmission
64-level greyscale

Advanced fax features: Broadcasting /Polling /Group dialling / Next fax reservation / Call reservation /Delayed transmission / Remote activation /Fax forwarding /Remote retrieval /Electronic cover page

Copy

Up to 99 multiple copies of each page loaded in the ADF
Reduce or increase document sizes from 50% to 150%

Additional Features

Help list of basic operational steps and functions
TAD interface for connecting external telephone devices

Weights and Measures

Power consumption: standby under 4.4W, peak 160W
Dimensions (WxDxH): 302mm x 267mm x 340mm
Weight 2.7kg

Consumables

PC-75, 1 x cassette including 144 sheet ribbon
PC-71RF, 1 x 144 sheet ribbon
PC-72RF, 2 x 144 sheet ribbon
PC-74RF, 4 x 144 sheet ribbon

* Purchased from the telephone company



Contact:

At your side.
brother.

Brother International Europe Ltd

Brother House, 1 Tame Street, Audenshaw, Manchester M34 5JE
Tel: +44 (0) 161 330 6531 Fax +44 (0) 161 330 5520.
Web-site: www.brother.com

Specifications correct at time of printing. Brother is a registered trademark of Brother Industries Ltd. Brand product names are registered trademarks or trademarks of their respective companies