

Fuse - FUSE 10,3X38 15A PV - 3061348

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Fuse, 10.3x38 mm, up to 1000 V DC, gPV characteristics

Your advantages

- ✓ 10 x 38 midget fuses for reliable protection of PV modules and their control system
- ✓ Use in PV lines with a nominal voltage of up to 1000 V DC
- ✓ Designed in accordance with the photovoltaic standard IEC 60269-6



Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 929448
GTIN	4046356929448
Weight per Piece (excluding packing)	8.830 g
Custom tariff number	85361050
Country of origin	Slovenia
Sales Key	BE1Z4X

Technical data

General

Color	white
-------	-------

Dimensions

Length	38 mm
Diameter	10.3 mm

General

Connection in acc. with standard	IEC 60269-6
Nominal current I_N	15 A

Fuse - FUSE 10,3X38 15A PV - 3061348

Technical data

General

Nominal voltage U_N	1000 V DC
Fuse	Midget / 10.3 x 38
Power dissipation	2.2 W
Melting integral I^2t	49 A ² s

Standards and Regulations

Connection in acc. with standard	IEC 60269-6
----------------------------------	-------------

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27142001
eCl@ss 11.0	27142001
eCl@ss 4.0	27142000
eCl@ss 4.1	27142000
eCl@ss 5.0	27142000
eCl@ss 5.1	27142000
eCl@ss 6.0	27142000
eCl@ss 7.0	27142001
eCl@ss 9.0	27142001

ETIM

ETIM 3.0	EC000035
ETIM 4.0	EC002704
ETIM 6.0	EC000035
ETIM 7.0	EC000035

UNSPSC

UNSPSC 6.01	30211915
UNSPSC 7.0901	39121514
UNSPSC 11	39121514
UNSPSC 12.01	39121514
UNSPSC 13.2	39121629
UNSPSC 18.0	39121629
UNSPSC 19.0	39121629
UNSPSC 20.0	39121629
UNSPSC 21.0	39121629

Fuse - FUSE 10,3X38 15A PV - 3061348

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU C- DE.BL08.B.00724
-----	---	--------------------------
