

## **Active power transducer**

G2BA480V12A 0...10V

Loadmonitors - GAMMA series

True power monitoring in 1- or 3-phase mains

Analog output 0...10V

Suitable for VFI (10 to 100Hz)

Zoom voltage 24V to 240V d.c. and 48V to 240V a.c.

Width 22.5mm

Industrial design



### **Technical data**

1. Functions

True power monitoring in 1- and 3-phase mains with analog output 0 ... 10V and the following settings which are selected by means of rotary switch:

Zero setting of zero point

(0%, 25%, 50%, 75% of nominal value)

Zero Fine fine setting of zero point (0% ... 25% of nominal value)

Span spar

. (100%, 75%, 50%, 25% of nominal value)

Range measuring range reversible between

0.75kW, 1.5kW, 3kW, 6kW

2. Indicators

Green LED U ON: indication of supply voltage Yellow LED's ON/OFF: indication analog output 0...10V

3. Mechanical design

Self-extinguishing plastic housing, IP rating IP40 Mounted on DIN-Rail TS 35 according to EN 60715

Mounting position: any

Shockproof terminal connection according to VBG 4 (PZ1 required),

IP rating IP20

Tightening torque: max. 1Nm

Terminal capacity:

1 x 0.5 to 2.5mm² with/without multicore cable end

1 x 4mm² without multicore cable end

2 x 0.5 to 1.5mm² with/without multicore cable end 2 x 2.5mm² flexible without multicore cable end

4. Input circuit

Supply voltage: 24V to 240V d.c. 48V to 240V a.c.

Terminals: A1-A2 (galvanically seperated)

Tolerance:

48V to 240V a.c. -15% to +10% 24V to 240V d.c. -20% to +25%

Rated frequency:

48 to 400Hz 48V to 240V a.c.
Rated consumption: 2.5VA (1.3W)
Duration of operation: 100%
Reset time: 500ms

Ripple and noise: -

Drop-out voltage: >30% of supply voltage

Overvoltage category: III (in accordance with IEC 60664-1)

Rated surge voltage: 4kV

5. Output circuit

 $\begin{array}{lll} \mbox{1 analog output} & 0...10V \\ \mbox{Terminals:} & \mbox{X1(+)} - \mbox{X2(-)} \\ \mbox{Settling time:} & \mbox{<450ms} \\ \mbox{Burden:} & \mbox{min. } 3k\Omega \\ \mbox{Galvanic isolation:} & 3kV DC \\ \end{array}$ 

6. Measuring circuit

Measuring range PN: reversible between 0.75kW, 1.5kW, 3kW, 6kW

Wave form

a.c. Sinus:
Sinus weighted PWM:
Measuring input voltage:
1-phase mains
3-phase mains
10 to 400Hz
10 to 100Hz
terminals L1-L2-L3
0 to 480V a.c.
3~ 0 to 480/277V

Overload capacity:

 $\begin{array}{lll} \mbox{1-phase mains} & 550 \mbox{V a.c.} \\ \mbox{3-phase mains} & 3 \mbox{\sim} 550 \mbox{/318V} \\ \mbox{Input resistance:} & 1.25 \mbox{M} \mbox{\Omega} \\ \mbox{Measuring input current:} & \mbox{terminal i-k} \\ \end{array}$ 

Measuring range 0.75kW, 1.5kW: 0 to 6A

Measuring range 3kW, 6kW: 0 to 12A (for I>8A distance >5mm)

Overload capacity: 12A permanent Input resistance:  $<10m\Omega$ 

Overvoltage category: III (in accordance with IEC 60664-1)

Rated surge voltage: 4k\

7. Accuracy

Base accuracy: ±2% (of maximum scale value)

Frequency influence: ±0.025% / Hz
Voltage influence: Temperature influence: ≤0.05% / °C

8. Ambient conditions

Ambient temperature: -25 to +55°C

(in accordance with IEC 60068-1)

Storage temperature: -25 to +70°C
Transport temperature: -25 to +70°C
Relative humidity: 15% to 85%

(in accordance with IEC 60721-3-3

Klasse 3K3)

Pollution degree: 3 (in accordance with IEC 60664-1)

Vibration resistance: 10 to 55Hz 0.35mm


(in accordance with IEC 60068-2-6)

Shock resistance: 15g 11ms


(in accordance with IEC 60068-2-27)

## **Functions**


#### Zero = 0% / Span = 25% ; Zero = 0% / Span = 100%




Zero = 25% / Span = 25% ; Zero = 25% / Span = 75%




Zero = 37,5% / Span = 50% ; Zero = 37,5% / Span = 100%




## **Connections**





# **Dimensions**



RELEASE 2011/11

Subject to alterations and errors

