



SIMATIC ET 200SP HA, digital output module, DQ 32X24VDC/0.5A HA, suitable for terminal block, H1, N0, color code CC00, channel diagnostics



Figure similar

General information	
Product type designation	DQ 32x24VDC/0.5A HA
Firmware version	V1.0
<ul style="list-style-type: none"> FW update possible 	Yes
Color code for module-specific color-coded label	CC00
Product function	
<ul style="list-style-type: none"> I&M data 	Yes; I&M0 to I&M3
Engineering with	
<ul style="list-style-type: none"> STEP 7 TIA Portal configurable/integrated from version 	V16
<ul style="list-style-type: none"> STEP 7 configurable/integrated from version 	V5.6
<ul style="list-style-type: none"> PCS 7 configurable/integrated from version 	V9.0
<ul style="list-style-type: none"> PCS neo can be configured/integrated from version 	V3.0
<ul style="list-style-type: none"> PROFINET from GSD version/GSD revision 	GSDML V2.3
Operating mode	
<ul style="list-style-type: none"> DQ 	Yes
<ul style="list-style-type: none"> DQ with energy-saving function 	No
<ul style="list-style-type: none"> PWM 	No
<ul style="list-style-type: none"> Oversampling 	No
Redundancy	
<ul style="list-style-type: none"> Redundancy capability 	No
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption (rated value)	60 mA; without load
Current consumption, max.	70 mA; without load
Output voltage	
Rated value (DC)	24 V
Power loss	
Power loss, typ.	1.6 W; minimum - typ. specification not possible because load-dependent
Address area	
Address space per module	
<ul style="list-style-type: none"> Inputs 	4 byte; QI of the outputs

• Outputs	4 byte
Digital outputs	
Number of digital outputs	32
Current-sinking	No
Current-sourcing	Yes
Digital outputs, parameterizable	Yes
Short-circuit protection	Yes; Clocked electronically
• Response threshold, typ.	2 A; Overload / short circuit
Open-circuit detection	No
Overload protection	Yes
Limitation of inductive shutdown voltage to	Typ. L+ (-53 V)
Controlling a digital input	Yes
Switching capacity of the outputs	
• with resistive load, max.	0.5 A
• on lamp load, max.	5 W
Load resistance range	
• lower limit	48 Ω
• upper limit	4 kΩ
Output current	
• for signal "1" rated value	0.5 A
• for signal "0" residual current, max.	0.1 mA
Output delay with resistive load	
• "0" to "1", typ.	54 μs
• "1" to "0", typ.	48 μs
Parallel switching of two outputs	
• for uprating	No
• for redundant control of a load	Yes; only outputs of the same group
Switching frequency	
• with resistive load, max.	100 Hz
• with inductive load, max.	2 Hz
• on lamp load, max.	10 Hz
Total current of the outputs	
• Current per channel, max.	0.5 A
• Current per module, max.	10 A
Total current of the outputs (per module)	
horizontal installation	
— up to 70 °C, max.	10 A
vertical installation	
— up to 60 °C, max.	10 A
Cable length	
• shielded, max.	1 000 m
• unshielded, max.	600 m
Interrupts/diagnostics/status information	
Diagnostics function	Yes
Substitute values connectable	Yes
Alarms	
• Diagnostic alarm	Yes
Diagnoses	
• Monitoring the supply voltage	Yes
— parameterizable	Yes
• Wire-break	No
• Short-circuit	Yes
• Short-circuit to M	Yes; channel by channel
• Short-circuit to L+	No
• Group error	Yes
Diagnostics indication LED	
• MAINT LED	Yes; Yellow LED
• Monitoring of the supply voltage (PWR-LED)	Yes; green PWR LED
• Channel status display	Yes; green LED

- for channel diagnostics
- for module diagnostics

No
Yes; green/red DIAG LED

Potential separation

Potential separation channels

- between the channels
- between the channels and backplane bus

No
Yes

Isolation

Isolation tested with 1 500 V DC/1 min, type test

Ambient conditions

Ambient temperature during operation

- horizontal installation, min.
- horizontal installation, max.
- vertical installation, min.
- vertical installation, max.

-40 °C
70 °C
-40 °C
60 °C

Dimensions

Width 22.5 mm
Height 115 mm
Depth 138 mm

Weights

Weight, approx. 150 g

Classifications

	Version	Classification
eClass	14	27-24-26-04
eClass	12	27-24-26-04
eClass	9.1	27-24-26-04
eClass	9	27-24-26-04
eClass	8	27-24-26-04
eClass	7.1	27-24-26-04
eClass	6	27-24-26-04
ETIM	10	EC001599
ETIM	9	EC001599
ETIM	8	EC001599
ETIM	7	EC001599

Approvals / Certificates

General Product Approval



[Miscellaneous](#)

[China RoHS](#)



General Product Approval

For use in hazardous locations



[Declaration of Conformity](#)



For use in hazardous locations

Maritime application



[Miscellaneous](#)



Maritime application

Environment



[NK / Nippon Kaiji Kyokai](#)



[CCS \(China Classification Society\)](#)



last modified:

10/23/2025