



Application Tooling > Hand Crimping Tools



Tool Grade: **Commercial Crimp Tooling**
Ratchet Configuration: **Operator Releasable & Adjustable**
Die Sets Type: **Fixed In Tool**
Specification Type: **TE Product Specification (114-)**
TE Certification: **Upon Request for Fee**

Features

Other

Crimp Form-Wire Barrel Type	Open Barrel - F Crimp
Tool Grade	Commercial Crimp Tooling
Ratchet Configuration	Operator Releasable & Adjustable
Die Sets Type	Fixed In Tool
Specification Type	TE Product Specification (114-)
TE Certification	Upon Request for Fee
Power Technology Type	Manual
Tooling Type	Straight Action Hand Tool

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per



homogenous material. Also BFR/CFR/PVC Free

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #1SNK160011R0000
MC812PA 1->10 (x10) Horizontal




TE Part #1SNK508310R0000
ZS10-ST



TE Part #926824-4
AM WIRE PIN 17-13 0.32MM PTPB




TE Part #BSA107N00480236000
923 PLUG, SHORT



TE Part #5068094006
CGPT-12.7/6.4-2-SP



TE Part #2-1879074-2
THS15 47R 5%



TE Part #539951-2
ERGO DIE MCP 2,8K



TE Part #1-1987558-3
PHOTOVOLTAIK CONNECTOR, 4sqmm



TE Part #4-1105051-1
HN.D-C-BU.AG.1,5



TE Part #1-1103637-1
HE.10.BU.S

Documents

Product Drawings



CSV10 CRIMPING HANDTOOL SOLARLOK 4-6

English

Datasheets & Catalog Pages

CONNECTIVITY_SYSTEMS_FOR_PV_INSTALLERS_3-1773458-6

English

SOLARLOK_CONNECTIVITY_SYSTEMS_FOR_PV_MANUFACTURERS_3-1773458-7

English

Bottoming Dies

English

AMERICAS_VERSION_SOLARLOK_INSTALLATION_MANUAL_2-1773458-2

English

6-1773461-4_SOLARLOK_1-RAIL_JUN_BOX_CH

Product Specifications

INSTRUCTION SHEET

English

Instruction Sheets

Instruction Sheet (non U.S.)

English