



**The Professional's Choice**

## SAFETY DATA SHEET

### 1. IDENTIFICATION OF THE MATERIAL AND SUPPLIER

#### 1.1 Product identifier

**Product name** MS HIGH PERFORMANCE ADHESIVE SEALANT  
**Synonyms** 8361, 8362, 8363, 8364 - PRODUCT CODE(S) • CRC MS HIGH PERFORMANCE ADHESIVE SEALANT

#### 1.2 Uses and uses advised against

**Uses** ADHESIVE • SEALANT • SILICONE SEALANT

#### 1.3 Details of the supplier of the product

**Supplier name** CRC INDUSTRIES (AUST) PTY LIMITED  
**Address** 9 Gladstone Road, Castle Hill, NSW, 2154, AUSTRALIA  
**Telephone** (02) 9849 6700  
**Fax** (02) 9680 4914  
**Email** [info.au@crcind.com](mailto:info.au@crcind.com)  
**Website** [www.crcindustries.com.au](http://www.crcindustries.com.au)

#### 1.4 Emergency telephone numbers

**Emergency** 13 11 26 (PIC)

### 2. HAZARDS IDENTIFICATION

#### 2.1 Classification of the substance or mixture

NOT CLASSIFIED AS HAZARDOUS ACCORDING TO SAFE WORK AUSTRALIA CRITERIA

#### 2.2 GHS Label elements

No signal word, pictograms, hazard or precautionary statements have been allocated.

#### 2.3 Other hazards

No information provided.

### 3. COMPOSITION/ INFORMATION ON INGREDIENTS

#### 3.1 Substances / Mixtures

Ingredient	CAS Number	EC Number	Content
SILOXANES AND SILICONES, DIMETHYL, HYDROXY TERMINATED	70131-67-8	615-070-3	>60%
CALCIUM CARBONATE	471-34-1	207-439-9	30 to 60%
TITANIUM DIOXIDE	13463-67-7	236-675-5	1 to 10%

### 4. FIRST AID MEASURES

#### 4.1 Description of first aid measures

**Eye** If in eyes, hold eyelids apart and flush continuously with running water. Continue flushing until advised to stop by a Poisons Information Centre, a doctor, or for at least 15 minutes.

**Inhalation** If inhaled, remove from contaminated area. Apply artificial respiration if not breathing.

**Skin** If skin or hair contact occurs, remove contaminated clothing and flush skin and hair with running water. Continue flushing with water until advised to stop by a Poisons Information Centre or a doctor.

**Ingestion** For advice, contact a Poisons Information Centre on 13 11 26 (Australia Wide) or a doctor (at once).

**PRODUCT NAME MS HIGH PERFORMANCE ADHESIVE SEALANT**

**First aid facilities** Eye wash facilities and safety shower should be available.

**4.2 Most important symptoms and effects, both acute and delayed**

See Section 11 for more detailed information on health effects and symptoms.

**4.3 Immediate medical attention and special treatment needed**

Treat symptomatically.

---

**5. FIRE FIGHTING MEASURES**

---

**5.1 Extinguishing media**

Use an extinguishing agent suitable for the surrounding fire.

**5.2 Special hazards arising from the substance or mixture**

Non flammable. May evolve toxic gases (carbon/ silicon oxides, hydrocarbons, acetic acid, formaldehyde) when heated to decomposition.

**5.3 Advice for firefighters**

Treat as per requirements for surrounding fires. Evacuate area and contact emergency services. Remain upwind and notify those downwind of hazard. Wear full protective equipment including Self Contained Breathing Apparatus (SCBA) when combating fire. Use waterfog to cool intact containers and nearby storage areas.

**5.4 Hazchem code**

None allocated.

---

**6. ACCIDENTAL RELEASE MEASURES**

---

**6.1 Personal precautions, protective equipment and emergency procedures**

Wear Personal Protective Equipment (PPE) as detailed in section 8 of the SDS. Clear area of all unprotected personnel. Ventilate area where possible. Contact emergency services where appropriate.

**6.2 Environmental precautions**

Prevent product from entering drains and waterways.

**6.3 Methods of cleaning up**

Contain spillage, then cover / absorb spill with non-combustible absorbent material (vermiculite, sand, or similar), collect and place in suitable containers for disposal. Eliminate all sources of ignition.

**6.4 Reference to other sections**

See Sections 8 and 13 for exposure controls and disposal.

---

**7. HANDLING AND STORAGE**

---

**7.1 Precautions for safe handling**

Before use carefully read the product label. Use of safe work practices are recommended to avoid eye or skin contact and inhalation. Observe good personal hygiene, including washing hands before eating. Prohibit eating, drinking and smoking in contaminated areas.

**7.2 Conditions for safe storage, including any incompatibilities**

Store in a cool, dry, well ventilated area, removed from incompatible substances, heat or ignition sources and foodstuffs. Ensure containers are adequately labelled, protected from physical damage and sealed when not in use. Check regularly for leaks or spills. Large storage areas should have appropriate fire protection systems.

**7.3 Specific end uses**

No information provided.

## 8. EXPOSURE CONTROLS / PERSONAL PROTECTION

### 8.1 Control parameters

#### Exposure standards

Ingredient	Reference	TWA		STEL	
		ppm	mg/m <sup>3</sup>	ppm	mg/m <sup>3</sup>
Calcium carbonate (Limestone, Marble, Whiting)	SWA [AUS]	--	10	--	--
Titanium dioxide (a)	SWA [AUS]	--	10	--	--

#### Biological limits

No biological limit values have been entered for this product.

### 8.2 Exposure controls

#### Engineering controls

Avoid inhalation. Use in well ventilated areas. Where an inhalation risk exists, mechanical extraction ventilation is recommended.

#### PPE

<b>Eye / Face</b>	Wear splash-proof goggles.
<b>Hands</b>	Wear PVC or rubber gloves. When using large quantities or where heavy contamination is likely, wear viton® gloves.
<b>Body</b>	When using large quantities or where heavy contamination is likely, wear coveralls.
<b>Respiratory</b>	Where an inhalation risk exists, wear a Type A (Organic vapour) respirator.



## 9. PHYSICAL AND CHEMICAL PROPERTIES

### 9.1 Information on basic physical and chemical properties

<b>Appearance</b>	VISCOUS COLOURED PASTE
<b>Odour</b>	SLIGHT ODOUR
<b>Flammability</b>	NON FLAMMABLE
<b>Flash point</b>	NOT RELEVANT
<b>Boiling point</b>	NOT AVAILABLE
<b>Melting point</b>	NOT AVAILABLE
<b>Evaporation rate</b>	NOT AVAILABLE
<b>pH</b>	NOT AVAILABLE
<b>Vapour density</b>	NOT AVAILABLE
<b>Specific gravity</b>	NOT AVAILABLE
<b>Solubility (water)</b>	INSOLUBLE
<b>Vapour pressure</b>	NOT AVAILABLE
<b>Upper explosion limit</b>	NOT RELEVANT
<b>Lower explosion limit</b>	NOT RELEVANT
<b>Partition coefficient</b>	NOT AVAILABLE
<b>Autoignition temperature</b>	NOT AVAILABLE
<b>Decomposition temperature</b>	NOT AVAILABLE
<b>Viscosity</b>	NOT AVAILABLE
<b>Explosive properties</b>	NOT AVAILABLE
<b>Oxidising properties</b>	NOT AVAILABLE
<b>Odour threshold</b>	NOT AVAILABLE

## 10. STABILITY AND REACTIVITY

### 10.1 Reactivity

Carefully review all information provided in sections 10.2 to 10.6.

## PRODUCT NAME MS HIGH PERFORMANCE ADHESIVE SEALANT

### 10.2 Chemical stability

Stable under recommended conditions of storage.

### 10.3 Possibility of hazardous reactions

Hazardous polymerisation is not expected to occur.

### 10.4 Conditions to avoid

Avoid heat, sparks, open flames and other ignition sources. Avoid exposure to moisture.

### 10.5 Incompatible materials

Incompatible with oxidising agents (e.g. hypochlorites), acids (e.g. nitric acid), alkalis (e.g. sodium hydroxide), heat and ignition sources.

### 10.6 Hazardous decomposition products

May evolve toxic gases (carbon/silicon oxides, hydrocarbons, acetic acid, formaldehyde) when heated to decomposition.

---

## 11. TOXICOLOGICAL INFORMATION

---

### 11.1 Information on toxicological effects

**Acute toxicity** Based on available data, the classification criteria are not met.

**Information available for the ingredients:**

Ingredient	Oral LD50	Dermal LD50	Inhalation LC50
SILOXANES AND SILICONES, DIMETHYL, HYDROXY TERMINATED	> 62,080 mg/kg (rat)	> 15,520 mg/kg (rabbit)	--
CALCIUM CARBONATE	> 2000 mg/kg (rat)	> 2000 mg/kg (rat)	> 3.0 mg/L
TITANIUM DIOXIDE	5000 mg/kg (rat)	--	3.43 - 6.82 mg/L air (rat)

<b>Skin</b>	Not classified as a skin irritant. Contact may result in mild irritation, redness and rash.
<b>Eye</b>	Not classified as an eye irritant. Contact may result in mild irritation, lacrimation and redness.
<b>Sensitisation</b>	Not classified as causing skin or respiratory sensitisation. Formaldehyde may be evolved which is a skin sensitiser. However, over exposure is not anticipated under normal conditions of use.
<b>Mutagenicity</b>	Not classified as a mutagen.
<b>Carcinogenicity</b>	Not classified as a carcinogen. Formaldehyde may be evolved during curing/decomposition which is classified as a confirmed human carcinogen (IARC Group 1). Titanium dioxide is classified as possibly carcinogenic to humans (IARC Group 2B). However, due to product form (ie. liquid) the risk of exposure is greatly reduced.
<b>Reproductive</b>	Not classified as a reproductive toxin.
<b>STOT - single exposure</b>	Over exposure to vapours may result in mild irritation of the nose and throat, with coughing. Acetic acid may be evolved which is a respiratory irritant. However, over exposure is not anticipated under normal conditions of use.
<b>STOT - repeated exposure</b>	Not classified as causing organ damage from repeated exposure.
<b>Aspiration</b>	Not classified as causing aspiration.

---

## 12. ECOLOGICAL INFORMATION

---

### 12.1 Toxicity

No information provided.

### 12.2 Persistence and degradability

No information provided.

### 12.3 Bioaccumulative potential

No information provided.

### 12.4 Mobility in soil

No information provided.

### 12.5 Other adverse effects

No information provided.

### 13. DISPOSAL CONSIDERATIONS

#### 13.1 Waste treatment methods

**Waste disposal** For small amounts, absorb with sand, vermiculite or similar and dispose of to an approved landfill site. For large quantities, contact the manufacturer/supplier for additional information. Prevent contamination of drains and waterways as aquatic life may be threatened and environmental damage may result.

**Legislation** Dispose of in accordance with relevant local legislation.

### 14. TRANSPORT INFORMATION

NOT CLASSIFIED AS A DANGEROUS GOOD BY THE CRITERIA OF THE ADG CODE, IMDG OR IATA

	LAND TRANSPORT (ADG)	SEA TRANSPORT (IMDG / IMO)	AIR TRANSPORT (IATA / ICAO)
<b>14.1 UN Number</b>	None allocated.	None allocated.	None allocated.
<b>14.2 Proper Shipping Name</b>	None allocated.	None allocated.	None allocated.
<b>14.3 Transport hazard class</b>	None allocated.	None allocated.	None allocated.
<b>14.4 Packing Group</b>	None allocated.	None allocated.	None allocated.

#### 14.5 Environmental hazards

No information provided.

#### 14.6 Special precautions for user

**Hazchem code** None allocated.

### 15. REGULATORY INFORMATION

#### 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

**Poison schedule** A poison schedule number has not been allocated to this product using the criteria in the Standard for the Uniform Scheduling of Medicines and Poisons (SUSMP).

**Classifications** Safework Australia criteria is based on the Globally Harmonised System (GHS) of Classification and Labelling of Chemicals.

**Inventory listings** **AUSTRALIA: AIIC (Australian Inventory of Industrial Chemicals)**  
All components are listed on AIIC, or are exempt.

### 16. OTHER INFORMATION

**Additional information**

**RESPIRATORS:** In general the use of respirators should be limited and engineering controls employed to avoid exposure. If respiratory equipment must be worn ensure correct respirator selection and training is undertaken. Remember that some respirators may be extremely uncomfortable when used for long periods. The use of air powered or air supplied respirators should be considered where prolonged or repeated use is necessary.

**SILICONE SEALANTS:** Toxic vapours released upon curing may result in eye and respiratory tract irritation. A hazard exists when high concentrations are generated in poorly ventilated areas. Once curing is complete, irritating or toxic vapours should no longer be evolved and therefore an inhalation hazard is no longer anticipated. In this cured state the sealant is considered inert and relatively non toxic.

**PERSONAL PROTECTIVE EQUIPMENT GUIDELINES:**  
The recommendation for protective equipment contained within this report is provided as a guide only. Factors such as form of product, method of application, working environment, quantity used, product concentration and the availability of engineering controls should be considered before final selection of personal protective equipment is made.

**PRODUCT NAME MS HIGH PERFORMANCE ADHESIVE SEALANT****HEALTH EFFECTS FROM EXPOSURE:**

It should be noted that the effects from exposure to this product will depend on several factors including: form of product; frequency and duration of use; quantity used; effectiveness of control measures; protective equipment used and method of application. Given that it is impractical to prepare a report which would encompass all possible scenarios, it is anticipated that users will assess the risks and apply control methods where appropriate.

**Abbreviations**

ACGIH	American Conference of Governmental Industrial Hygienists
CAS #	Chemical Abstract Service number - used to uniquely identify chemical compounds
CNS	Central Nervous System
EC No.	EC No - European Community Number
EMS	Emergency Schedules (Emergency Procedures for Ships Carrying Dangerous Goods)
GHS	Globally Harmonized System
GTEPG	Group Text Emergency Procedure Guide
IARC	International Agency for Research on Cancer
LC50	Lethal Concentration, 50% / Median Lethal Concentration
LD50	Lethal Dose, 50% / Median Lethal Dose
mg/m <sup>3</sup>	Milligrams per Cubic Metre
OEL	Occupational Exposure Limit
pH	relates to hydrogen ion concentration using a scale of 0 (high acidic) to 14 (highly alkaline).
ppm	Parts Per Million
STEL	Short-Term Exposure Limit
STOT-RE	Specific target organ toxicity (repeated exposure)
STOT-SE	Specific target organ toxicity (single exposure)
SUSMP	Standard for the Uniform Scheduling of Medicines and Poisons
SWA	Safe Work Australia
TLV	Threshold Limit Value
TWA	Time Weighted Average

**Report status**

This document has been compiled by RMT on behalf of the manufacturer, importer or supplier of the product and serves as their Safety Data Sheet ('SDS').

It is based on information concerning the product which has been provided to RMT by the manufacturer, importer or supplier or obtained from third party sources and is believed to represent the current state of knowledge as to the appropriate safety and handling precautions for the product at the time of issue. Further clarification regarding any aspect of the product should be obtained directly from the manufacturer, importer or supplier.

While RMT has taken all due care to include accurate and up-to-date information in this SDS, it does not provide any warranty as to accuracy or completeness. As far as lawfully possible, RMT accepts no liability for any loss, injury or damage (including consequential loss) which may be suffered or incurred by any person as a consequence of their reliance on the information contained in this SDS.

**Prepared by**

Risk Management Technologies  
5 Ventnor Ave, West Perth  
Western Australia 6005  
Phone: +61 8 9322 1711  
Fax: +61 8 9322 1794  
Email: [info@rmt.com.au](mailto:info@rmt.com.au)  
Web: [www.rmtglobal.com](http://www.rmtglobal.com)

**[ End of SDS ]**