

PRODUCT DATASHEET

P RF CLAS BW 40 4 W/2700K E14

PARATHOM Retrofit CLASSIC BW | LED lamps, classic bulb shape



AREAS OF APPLICATION

- Perfect for decorative installations
- Domestic applications
- General illumination
- Outdoor use in outdoor luminaires only (minimum IP65)

PRODUCT BENEFITS

- Lamps with innovative LED "filament" technology
- Design, dimensions, luminous flux comparable to an incandescent or halogen lamp
- No UV and near-IR radiation in the light beam
- Instant 100 % light, no warm-up time
- Can be easily fitted instead of ordinary light bulbs
- Lower thermal output (compared with the standard reference product)

PRODUCT FEATURES

- Professional LED lamps for line voltage
- Beam angle: up to 300°
- Not dimmable
- Base: E14
- Mercury-free lamps
- Lifetime: up to 15,000 h



TECHNICAL DATA

Electrical data

Rated wattage	4.00 W
Nominal wattage	4.00 W
Nominal voltage	220...240 V
Max. lamp no. on circuit break. 10 A (B)	156
Max. lamp no. on circuit break. 16 A (B)	250
Operating frequency	50...60 Hz
Power factor λ	> 0.40
Claimed equiv. conventional lamp power	40 W


Photometrical data

Nominal luminous flux	470 lm
Rated luminous flux	470 lm
Lumen main.fact.at end of nom.life time	0.70
Light color (designation)	Warm White
Color temperature	2700 K
Luminous flux	470 lm
Color rendering index Ra	≥ 80
Standard deviation of color matching	≤ 6 sdc _m
Rated color temperature	2700 K

Light technical data

Warm-up time (60 %)	< 0.50 s
Starting time	< 0.5 s

Dimensions & weight



Overall length	100.0 mm
Diameter	35.0 mm

Outer bulb	B35
Length	97.0 mm

Temperatures & operating conditions

Ambient temperature range	-20...+40 °C
Maximum temperature at tc test point	58 °C

Lifespan

Nominal lamp life time	15000 h
Rated lamp life time	15000 h
Number of switching cycles	100000

Additional product data

Base (standard designation)	E14
Mercury content	0.0 mg
Mercury-free	Yes
Design / version	Clear
Show WEEE picto	Yes
Product remark	All technical parameters apply to the entire lamp/Due to the complex production process for light-emitting diodes, the typical values shown for the technical LED parameters are purely statistical values that do not necessarily match the actual technical parameters of each individual product, which can vary from the typical value

Capabilities

Dimmable	No
-----------------	----

Certificates & standards

Energy efficiency class	A++
Energy consumption	4 kWh/1000h

Country-specific categorizations

ILCOS	DRBB/C-4/827-220/240-E14-35
Order reference	LEDPCLBW40 4W/8

LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4052899961913	Folding carton box 1	39 mm x 39 mm x 109 mm	27.50 g	0.17 dm ³
4052899962408	Shipping carton box 10	205 mm x 87 mm x 123 mm	318.00 g	2.19 dm ³

4058075287921	Folding carton box 1	39 mm x 39 mm x 109 mm	30.00 g	0.17 dm ³
4058075287938	Shipping carton box 10	205 mm x 87 mm x 123 mm	348.00 g	2.19 dm ³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.