



Drawings not to scale
All dimensions in mm

This omni-directional motion sensor has been designed to sense small vibrations and movements. The sensitivity is adjustable. The output is referenced to 0V and can drive a transistor or similar device.

The unit is fully encapsulated.

SPECIFICATION

SUPPLY VOLTAGE	Max. Vdc	5
SUPPLY CURRENT	Max. mA	40
OPERATING TEMPERATURE	Deg. °C	-10° + 70°
OUTPUT		24mA at 5Vdc
CASE MATERIAL		ABS
CABLE		PVC

MOTION SENSOR MODULE

PART NUMBER
MS 24A/30

Rev. No.	Revision Note	Date	Signature
A	Provisional	1-9-98	RG



BS5750/ISO 9000
Reg. No. FM 21080

As part of the company policy of continued product improvement, specifications may change without notice. Our sales office will be pleased to help you with the latest information on this product range and details of our full design and manufacturing service. All products are supplied to our standard conditions of sale otherwise agreed in writing.