




Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.




Compatible Parts




TE Part # 293302-1
NECTOR S CHASSIS MOUNT FRAME

Customers Also Bought



TE Part #2-2176400-0
3540 6R2 1%



TE Part #2-2176400-4
3540 9R1 1%



TE Part #T4171210002-001
M12,FRONT MOUNTING,MALE,A,2P,
0.2M WIRE




TE Part #293286-3
ASS'Y WALL OUTLET FRAME BLACK



TE Part #1986715-8
PWR TB 2PIN 8P,15.00 PCB-FLANGE



TE Part #293302-1
NECTOR S CHASSIS MOUNT FRAME



TE Part #5-2176391-8
RQ 1206 48K7 0.1% 10PPM 5K RL



TE Part #104439-1
10X2 MTE RCPT SR PLAIN .100CL



TE Part #293286-2
ASS'Y WALL OUTLET FRAME GRAY



TE Part #293315-4
NECTOR S PCB CONN. ASSY 90 DEG
OUTLET

Documents

- CAD Files

Customer View Model

ENG_CVM_293303-1_A1.3d_igs.zip

English
- Customer View Model

ENG_CVM_293303-1_A1.3d_stp.zip

English



Customer View Model

[ENG_CVM_293303-1_A1.2d_dxf.zip](#)

English

[3D PDF](#)

English

Customer View Model

[ENG_CVM_CVM_293303-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_293303-1_A.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_293303-1_A.2d_dxf.zip](#)

English

[3D PDF](#)

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[NECTOR_S_LINE_CONNECTOR_BROCHURE](#)

English

Product Specifications

[Product Specification](#)

English