

## Product information

**34 42 130**

### Precision Electronics Gripping Pliers

DIN ISO 9655



- For very precise assembly work, e.g. in electronics and fine mechanics
- For gripping, holding and bending
- With precision laser cut cross-shaping
- Approx. 20% lighter than conventional electronics pliers
- Bolted joint and carefully manufactured joint surfaces for even, low-friction movement throughout the entire opening range
- Smooth-running double spring for a gentle and even opening
- Ergonomically optimised multi-component handles
- Flat, wide jaws
- With precision laser cut cross-shaping
- Ball bearing chrome steel, forged, multi stage oil-hardened




#### General

Article No.	34 42 130
EAN	4003773080282
Pliers	burnished
Head	polished
Handles	with multi-component grips
Weight	61 g
Dimensions	130 x 51 x 20 mm
Standard	DIN ISO 9655
REACH compliant	no
RohS compliant	no

#### Technical details

Jaw length (B)	21.9 mm
Jaw thickness (joint) (D)	6.5 mm
Tips width (E)	1.4 mm
Tips thickness (F)	3.5 mm
Head width (A)	11.2 mm



## Classification

eCl@ss 5.1.4	21040301
proficl@ss 6.0	EAA840c015
UNSPSC 13.1	27112149

*technical change and errors excepted*

