



input coupler with integrated relay, 24 V AC/DC, 1 change-over contact, spring-loaded terminal (push-in), width 6.2 mm, thermal current 6 A

product brand name	SIRIUS
product category	SIRIUS 3RQ4 coupling relay, narrow design
product designation	Coupling relay with integrated relay output
design of the product	input coupling link
product type designation	3RQ4
General technical data	
display version LED	Yes
product feature protective coating on printed-circuit board	No
product component	
• relay output	Yes
• semi-conductor output	No
power loss [W] maximum	0.25 W
consumed active power	0.3 W
insulation voltage for overvoltage category III according to IEC 60664 with degree of pollution 3 rated value	300 V
surge voltage resistance rated value	4 kV
maximum permissible voltage for protective separation	
• between control and auxiliary circuit	300 V
• between control and auxiliary circuit according to IEC 60947-1	300 V
percental drop-out voltage related to the input voltage	10 %
flammability class of enclosure material	UL94 V-0
shock resistance	
• according to IEC 60068-2-27	sinusoidal half-wave 15g / 11 ms
vibration resistance	
• according to IEC 60068-2-6	6 ... 150 Hz: 2 g
operating frequency maximum	72 000 1/h
switching behavior	monostable
mechanical service life (operating cycles) typical	10 000 000
electrical endurance (operating cycles)	
• at AC-15 at 250 V typical	100 000
thermal current	6 A
reference code according to IEC 81346-2	K
Substance Prohibitance (Date)	09/26/2024
Weight	34 g
Control circuit/ Control	
control supply voltage at AC	
• at 50 Hz rated value	24 V
• at 60 Hz rated value	24 V
control supply voltage frequency	
• 1 rated value	50 Hz

• 2 rated value	60 Hz
control supply voltage at DC rated value	24 V
operating range factor control supply voltage rated value at DC	
• initial value	0.85
• full-scale value	1.25
operating range factor control supply voltage rated value at AC at 50 Hz	
• initial value	0.8
• full-scale value	1.25
operating range factor control supply voltage rated value at AC at 60 Hz	
• initial value	0.8
• full-scale value	1.25
ON-delay time	
• at AC maximum	10 ms
• at DC maximum	10 ms
OFF-delay time maximum	10 ms
Switching Function	
design of the switching function positively driven	No
Digital Outputs	
property of the output short-circuit proof	No
Mechanical data	
product component plug-in socket	No
design of the relay operating mechanism	poled
Short-circuit protection	
design of the fuse link for short-circuit protection of the auxiliary switch required	fuse gG: 4 A
Auxiliary circuit	
type of switching contact	Changeover contact
material of switching contacts	AgSnO ₂
number of CO contacts for auxiliary contacts	1
operational current of auxiliary contacts at AC-15	
• at 24 V	3 A
• at 250 V	3 A
operational current of auxiliary contacts at DC-13	
• at 24 V	1 A
• at 125 V	0.2 A
• at 250 V	0.1 A
contact reliability of auxiliary contacts	one incorrect switching operation of 100 million switching operations (17 V, 5 mA)
Main circuit	
type of voltage	AC/DC
ampacity of the output relay at AC-15 at 250 V at 50/60 Hz	3 A
ampacity of the output relay at DC-13	
• at 24 V	1 A
• at 125 V	0.2 A
• at 250 V	0.1 A
Electromagnetic compatibility	
electromagnetic compatibility	acc. to EN 60947-5-1
EMC emitted interference according to IEC 60947-1	ambience A (industrial sector)
EMC immunity according to IEC 60947-1	corresponds to degree of severity 3
conducted interference	
• due to burst according to IEC 61000-4-4	2 kV
• due to conductor-earth surge according to IEC 61000-4-5	2 kV
• due to conductor-conductor surge according to IEC 61000-4-5	1 kV
field-based interference according to IEC 61000-4-3	10 V/m
electrostatic discharge according to IEC 61000-4-2	6 kV contact discharge / 8 kV air discharge
Display	
display version as status display by LED	LED green
Safety related data	

B10d value		1 200 000
Connections/ Terminals		
product function removable terminal		No
type of electrical connection		
• for auxiliary and control circuit		spring-loaded terminals (push-in)
type of connectable conductor cross-sections		
• solid		1x (0.25 ... 2.5 mm ²)
• finely stranded with core end processing		1x (0.25 ... 1.5 mm ²)
• finely stranded without core end processing		1x (0.25 ... 2.5 mm ²)
• for AWG cables solid		1 x (20 ... 14)
• for AWG cables stranded		1x (20 ... 14)
connectable conductor cross-section		
• solid		0.25 ... 2.5 mm ²
• finely stranded with core end processing		0.25 ... 1.5 mm ²
• finely stranded without core end processing		0.25 ... 2.5 mm ²
AWG number as coded connectable conductor cross section		
• solid		20 ... 14
• stranded		20 ... 14
size of the screwdriver tip		PZ1
stripped length		10 mm
Installation/ mounting/ dimensions		
mounting position		any
fastening method		snap-on mounting
height		93 mm
width		6.2 mm
depth		84.5 mm
required spacing		
• with side-by-side mounting		
— forwards		0 mm
— backwards		0 mm
— upwards		0 mm
— downwards		0 mm
— at the side		0 mm
• for grounded parts		
— forwards		0 mm
— backwards		0 mm
— upwards		0 mm
— at the side		0 mm
— downwards		0 mm
• for live parts		
— forwards		0 mm
— backwards		0 mm
— upwards		0 mm
— downwards		0 mm
— at the side		0 mm
Ambient conditions		
installation altitude at height above sea level maximum		2 000 m
ambient temperature		
• during operation		-25 ... +60 °C
• during storage		-40 ... +85 °C
• during transport		-40 ... +85 °C
relative humidity during operation		10 ... 95 %
Approvals Certificates		
General Product Ap- proval	other	Environment



[Confirmation](#)



Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RQ4038-2AB00>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RQ4038-2AB00>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)


<https://support.industry.siemens.com/cs/ww/en/ps/3RQ4038-2AB00>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RQ4038-2AB00&lang=en

Characteristic: Derating

<https://support.industry.siemens.com/cs/ww/en/ps/3RQ4038-2AB00/manual>



last modified:

5/16/2025