

## The BL54L15 Series Goes to the Next Bluetooth® LE Level!

Experience a new pinnacle of performance, efficiency, and security with our new BL54L15 series, built on Nordic Semiconductor's powerful **nRF54L** silicon. Elevating what you know and love from the nRF52 series, this next generation redefines Bluetooth LE and 802.15.4 solutions. Unleashing enhanced processing power, expanded memory, and innovative peripherals, the BL54L15 is the ultimate choice for low power connectivity.

Powered by the **Nordic's nRF54L15** SoC, our compact BL54L15 modules deliver secure and robust Bluetooth LE and 802.15.4 with flexible programming via the Nordic nRFConnect SDK, Zephyr RTOS and Canvas.

Featuring a **128MHz ARM Cortex M33** and **128MHz RISC-V coprocessor**, supported by 1.5 MB non-volatile memory and 256 KB RAM, the BL54L15 modules offer double the processing power (vs prior BL654 – nRF52840). The BL54L15 series brings out all nRF54L15 hardware features and capabilities including up to **+7 dBm** transmit power, **1.7V – 3.5V** supply considerations, and **NFC A-Tag** implementation.

It's further enhanced with state-of-the-art security and is designed for PSA Certified level 3 and supports services such as Secure Boot, Secure Firmware Update, Secure Storage plus protection from physical attacks.

**Application Areas:** Building automation, security, medical peripherals, industrial sensors, and more.



- **Nordic nRF54L15** – 6x6 QFN48 with 31 GPIOs utilized.
- **Multi-protocol support:** Qualified against Bluetooth Core 6.0, 802.15.4 (Thread & Matter)
- **Cortex M33** processor core: 128 MHz ARM Cortex M33
- **RISC-V** co-processor core: 128 MHz VPR
- **Memory:** 1.5MB non-volatile memory, 256 KB RAM
- **High Speed Peripherals:** – HS-SPI/UART, software defined peripherals on 128 MHz VPR, GPIO – 1x 64 MHz Port, 1.7 – 3.5V, 11 GPIOs
- **Low Leakage Peripherals:** 2x QDEC, 7x Timer, Global RTC, 2x WDT, NFC A-Tag, TEMP, I2S, COMP, 3x PWM, LPCOMP, 14-bit 8CH ADC, 5x TWI/SPI/UART, GPIO (2x 16 MHz Port (P0, P1), 19 GPIO's, 1.7-3.5V, 31 GPIO)
- **Antenna choice** – integrated pre-certified **PCB Trace antenna** or external antenna support via **MHF4 connector**
- **Ultra-small footprint** (14 mm x 10 mm x 1.6 mm)
- **Extended Industrial Temperature Rating** (-40° to +105 °C)
- **Development choice:** Zephyr RTOS, Nordic nRF Connect SDK & Canvas
- **Bluetooth LE:** Channel Sounding, LE 2M, LE Coded, LE Secure Connections & more
- **Firmware Over the Air (FOTA)** via MCUboot and Zephyr
- **Hostless operation** – Multi Core MCU reduces BOM
- **Fully featured development kits** to jump start Bluetooth LE development
- Mechanically same form factor as **BL652 Series**
- **100% drop in** and pin for pin to **BL54L10 series**

## Key Features



### Best in Class Multiprotocol Radio

Best-in-class multiprotocol radio with up to 7 dBm TX power (with 1 dB steps) and -94 dBm RX sensitivity for 1 Mbps Bluetooth LE. Supports Bluetooth Core 6.0 including Channel Sounding



### Advanced Security

Designed for PSA Certified Level 3 with Secure Boot, Secure Firmware Update, and Secure Storage. Integrated tamper sensors detect attacks and take action, and cryptographic accelerators are hardened against side-channel attacks.



### True Industrial Operating Range

Designed and certified to the highest industrial temperature range of -40 °C to +105 °C for every component utilized.



### Global Approvals – Make Yourself at Home

Carries several modular FCC, ISCED, CE, UKCA, RCM, MIC, KC for Bluetooth LE & 802.15.4



### Personal Support from Design to Manufacture

Our industry-renowned support is passionate about helping you speed your design to market.



**NORDIC**  
SEMICONDUCTOR



Zephyr™ Project



CANVAS  
SOFTWARE SUITE

## Where We Help



### Wireless Connectivity

Enhanced processing power, expanded memory and innovative peripherals ideal for applications that require optimized, low power connectivity.



### Security Resilience

Security is top of mind with advanced security services that deliver greater protection, including PSA Certified level 3.



### Lifecycle Management

Designed for long product lifecycles, with options for scalability and futureproofing.



### Regulatory Compliance

Accredited EMC test facility, certification experience in 140 countries and continuous compliance monitoring.

## Specifications

Category	Feature	Specification
Wireless Specification	Bluetooth®	Qualified against Bluetooth Core 6.0
	802.15.4	Thread and Matter
	NFC	A-Tag
	Frequency	2.402 - 2.480 GHz
	Transmit Power	+ 7 dBm (maximum). Configurable down to -40 dBm
	Receive Sensitivity	-94 dBm (typical BLE 1 Mbps) -102 dBm (typical BLE 125 kbps)
	Link Budget	101 dB (@ Bluetooth LE 1 Mbps), 109 dB (@ Bluetooth LE 125 kbps)
	Antenna Options	PCB trace antenna or MHF4 connector for external antennas
Host Interface and Peripherals	Raw Data Rates (Air)	Bluetooth LE: 1 Mbps, 2 Mbps, 125 kbps, 500kps 802.15.4-2006: 250kbps
	UART Interface	TX, RX, CTS, RTS, DTR, DSR, DCD, RI (GPIO) Default: 19200, N, 8, 1. Configurable from 1200 bps to 1 Mbps
	Other	31 multifunction GPIO's that can provide: <ul style="list-style-type: none"> <li>• 5x UART/SPI/TWI</li> <li>• 8x ADC channels (1 pin each)</li> <li>• 2x I2S (5 GPIO pins)</li> <li>• 3x PWM output (1 GPIO pin per PWM)</li> <li>• 7x TIMER (no GPIO needed unless required)</li> <li>• 2 GPIO pins for 32.768 kHz crystal</li> <li>• 1x NFC (2 GPIO pins)</li> <li>• 2x QDEC</li> <li>• 20x Wakeup pins</li> </ul>
Features	Bluetooth LE	<ul style="list-style-type: none"> <li>• GATT client &amp; GATT server – Any adopted/custom services</li> <li>• Central/Peripheral roles</li> <li>• Mesh networking</li> <li>• LE CODED</li> <li>• LE 2M</li> <li>• Channel Sounding</li> <li>• LE Secure Connections</li> <li>• Extended Advertising</li> <li>• LE Power Control</li> <li>• DTM Firmware (Test Modes)</li> </ul>
Programmability Options	Nordic SDK	Software/Support available from Nordic directly <a href="https://devzone.nordicsemi.com/">https://devzone.nordicsemi.com/</a>
	Zephyr RTOS	Software/Support available from <a href="https://www.zephyrproject.org/">https://www.zephyrproject.org/</a>
	Canvas SW Suite	Software/ Support available from <a href="https://www.ezurio.com/canvas/software-suite">https://www.ezurio.com/canvas/software-suite</a>
FW upgrade		Via UART or JTAG
Supply Voltage		Normal Voltage Mode: 1.7V – 3.5V
Power Consumption	Current	Max Peak Radio Current (@ +7dBm TX) – 24 mA (supply voltage.8V) Max Peak Radio Current (@ -40 dBm TX) – 6.5 mA (supply voltage 1.8V)
Physical	Dimensions	14 mm x 10 mm x 1.6 mm
Environmental	Temp Range	-40°C to +105°C
Miscellaneous	Lead Free	Lead-free and RoHS-compliant
	Development Kit	Development board and free software tools
Development Tools	Utilities	Nordic nRFConnect - Android and iOS applications UART firmware upgrade Xbit Tools and utilities
Qualifications	Bluetooth®	Complete Declaration ID
Regulatory	Approvals	FCC, ISCED, EU, UKCA, RCM, MIC, KC – All BL54L15 Series are Bluetooth & 802.15.4 certified

For full specifications on BL54L15 modules, please see the appropriate datasheet.

## Ordering Information

Part	Description
453-00001R	Module, BL54L15, (Nordic nRF54L15), Trace antenna, Tape/Reel
453-00044R	Module, BL54L15, (Nordic nRF54L15), MHF4 Connector, Tape/Reel
453-00001C	Module, BL54L15, (Nordic nRF54L15), Trace antenna, Cut Tape
453-00044C	Module, BL54L15, (Nordic nRF54L15), MHF4 Connector, Cut Tape
453-00001-K1	Development kit, Module, BL54L15 (Nordic nRF54L15), Trace antenna
453-00044-K1	Development kit, Module, BL54L15 (Nordic nRF54L15), MHF4 Connector

Ezurio's products are subject to standard [Terms & Conditions](#).