

Rittal – The System.

Faster – better – everywhere.

► Rack-mounted fans for 482.6 mm (19") Air throughput 320 – 480m³/h – SK 3340.230

Date : Apr 26, 2021

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Rack-mounted fans for 482.6 mm (19") Air throughput 320 – 480m³/h – SK 3340.230

created: 26.04.2021 build on www.rittal.com/uk-en



Product description

Description: Rack-mounted fan for direct installation in the 482.6 mm (19") level. Installation allows air to circulate permanently inside the enclosure, thus preventing the formation of hot spots.

Colour: RAL 7035

Supply includes: Fully wired unit ready for connection
Terminal strip and assembly parts

Product description

Total cooling output/Number of fan modules:

Air throughput (unimpeded air flow): 320 m³/h

Rated operating voltage: 230 V, 1~, 50 Hz/60 Hz

Dimensions: Width: 482.6 mm
Height: 44 mm
Depth: 200 mm

Distance between axes of fans: 85 mm

Temperature range: Operation (environment): -10 °C...+55 °C

Rated current max.: At 50 Hz: 0.24 A
At 60 Hz: 0.22 A

Miniature circuit-breaker/fuse:	6 A
Noise level:	At 50 Hz: 51 dB(A)
No. of fans:	2
eCl@ss 8.0/8.1:	27180716
Packs of:	1 pc(s).
Weight/pack:	2.24 kg
EAN:	4028177041448
Customs tariff number:	84145915
ETIM 7.0:	EC000320
ETIM 6.0:	EC000320
eCl@ss 8.0/8.1:	27180716
eCl@ss 6.0/6.1:	27180716
Product description:	SK rack-mounted fan, for 482.6 mm (19"), 320 m ³ /h, 230 V, 1~, 50/60 Hz, WHD: 482.6 x 44 x 200 mm
Approvals	
Approvals:	Approval overview UR + C-UR
Certificates:	EAC
Declarations:	Declaration of conformity