



Changeover operating mechanism for vacuum contactor 3RT126 AC (50...60 Hz) / DC operation, 96 ... 127 V Operating mechanism: electronic with PLC input 24 V DC Screw terminal

|                                                           |                                                                                                                                                                                                                                               |     |                   |
|-----------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----|-------------------|
| product brand name                                        | SIRIUS                                                                                                                                                                                                                                        |     |                   |
| product category                                          | Solenoid coils                                                                                                                                                                                                                                |     |                   |
| product designation                                       | Changeover operating mechanism                                                                                                                                                                                                                |     |                   |
| product type designation                                  | 3RT19                                                                                                                                                                                                                                         |     |                   |
| General technical data                                    |                                                                                                                                                                                                                                               |     |                   |
| Substance Prohibittance (Date)                            | 05/01/2012                                                                                                                                                                                                                                    |     |                   |
| SVHC substance name                                       | Lead - 7439-92-1<br>Lead monoxide (lead oxide) - 1317-36-8<br>2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol - 79-94-7<br>6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol - 119-47-1<br>Perfluorobutane sulfonic acid (PFBS) and its salts - - |     |                   |
| Weight                                                    | 1.047 kg                                                                                                                                                                                                                                      |     |                   |
| type of voltage of the control supply voltage             | AC/DC                                                                                                                                                                                                                                         |     |                   |
| control supply voltage 1 at AC                            |                                                                                                                                                                                                                                               |     |                   |
| • at 50 Hz                                                | 96 ... 127 V                                                                                                                                                                                                                                  |     |                   |
| • at 60 Hz                                                | 96 ... 127 V                                                                                                                                                                                                                                  |     |                   |
| control supply voltage 2 at AC                            |                                                                                                                                                                                                                                               |     |                   |
| • at 50 Hz rated value                                    | 127 V                                                                                                                                                                                                                                         |     |                   |
| • at 60 Hz rated value                                    | 127 V                                                                                                                                                                                                                                         |     |                   |
| control supply voltage 1 at DC                            | 96 ... 127 V                                                                                                                                                                                                                                  |     |                   |
| control supply voltage 2 at DC rated value                | 127 V                                                                                                                                                                                                                                         |     |                   |
| apparent pick-up power of magnet coil at AC               |                                                                                                                                                                                                                                               |     |                   |
| • at 50 Hz                                                | 570 VA                                                                                                                                                                                                                                        |     |                   |
| • at 60 Hz                                                | 570 VA                                                                                                                                                                                                                                        |     |                   |
| inductive power factor with closing power of the coil     |                                                                                                                                                                                                                                               |     |                   |
| • at 50 Hz                                                | 0.8                                                                                                                                                                                                                                           |     |                   |
| • at 60 Hz                                                | 0.8                                                                                                                                                                                                                                           |     |                   |
| apparent holding power of magnet coil at AC               |                                                                                                                                                                                                                                               |     |                   |
| • at 50 Hz                                                | 5.6 VA                                                                                                                                                                                                                                        |     |                   |
| • at 60 Hz                                                | 5.6 VA                                                                                                                                                                                                                                        |     |                   |
| inductive power factor with the holding power of the coil |                                                                                                                                                                                                                                               |     |                   |
| • at 50 Hz                                                | 0.8                                                                                                                                                                                                                                           |     |                   |
| • at 60 Hz                                                | 0.8                                                                                                                                                                                                                                           |     |                   |
| Approvals Certificates                                    |                                                                                                                                                                                                                                               |     |                   |
| General Product Approval                                  |                                                                                                                                                                                                                                               | EMV | Test Certificates |



[Special Test Certificate](#)


[Confirmation](#)
[Miscellaneous](#)
[Special Test Certificate](#)
[Environmental Conformations](#)

## Further information

## Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

## Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

## Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

## Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RT1966-5NF31>


## Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RT1966-5NF31>

## Service&amp;Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RT1966-5NF31>

## Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3RT1966-5NF31&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RT1966-5NF31&lang=en)


last modified:

4/2/2025