

Part Number: 9708

Speaker Cable, 2 Conductor 18 AWG, High Conductivity, Siamese



Product Description

Speaker Cable, 18 AWG stranded (16x30) ETP high-conductivity copper conductors, PVC insulation, parallel: (1) tinned, (1) bare.

Technical Specifications

Product Overview

Environmental Space:	Indoor (Not Riser or Plenum)
Suitable Applications:	Speaker Cable

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
18	16x30	High Conductivity TC - Tinned Copper	1
18	16x30	BC - Bare Copper	1
Conductor Count:		2	
Conductor Size:		18 AWG	

Insulation

Material	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.032 in

Outer Shield Material

Material
Unshielded

Outer Jacket Material

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.11 x 0.22 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
6.48 Ohm/1000ft

Inductance

Nominal Inductance
0.22 μ H/ft

Current

Max. Recommended Current [A]
4.2 Amps per conductor @ 25°C

Voltage

Non-UL Voltage Rating

300 V RMS

Temperature Range

Non-UL Temp Rating:	60°C
Operating Temp Range:	-20°C To +60°C

Mechanical Characteristics

Bulk Cable Weight:	19 lbs/1000ft
Max Recommended Pulling Tension:	50 lbs
Min Bend Radius/Minor Axis:	2 in

Standards

CPR Euroclass:	Eca
----------------	-----

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Footnote
9708 3681000	Clear, Transparent	C
9708 368500	Clear, Transparent	
9708 368U1000	Clear, Transparent	
9708 368U500	Clear, Transparent	

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.