

# Eaton 189775

Catalog Number: 189775

Eaton Moeller series NZM - Molded Case Circuit Breaker.  
Undervoltage release for NZM2/3, 1 early-make auxiliary contact,  
2NO, 48AC, Push-in terminals

## General specifications



Product Name	Catalog Number
Eaton Moeller series NZM release	189775
EAN	Product Length/Depth
4015081877706	115 mm
Product Height	Product Width
65 mm	75 mm
Product Weight	Compliances
0.08 kg	IEC
	UL/CSA
	RoHS conform

## Product specifications

### Used with

NZM3(-4), N(S)3(-4)

NZM2(-4), N(S)2(-4)

### Type

Accessory Undervoltage release Undervoltage release with early-make auxiliary contact

### Special features

For interlocking and load-shedding circuits, as well as for early-make of the undervoltage release in main-switch applications. Instantaneous shut-off of the NZM circuit breaker when the control voltage drops below 35 - 70% Us. For use with emergency-stop devices in connection with an emergency-stop button. When the under-voltage trip is switched off, accidental contact with the circuit breaker's primary contacts is prevented when switched on. Early-make of auxiliary contacts on switching on and off (manual operation): approx. 20 ms (NZM2/3) and 90 ms (NZM4). Undervoltage release modules cannot be installed simultaneously with early-make contact NZM...-XHIV, shunt release NZM...-XA... or relays modules NZM...-X2A...

### 10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

### 10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

### 10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

### 10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

#### 10.2.2 Corrosion resistance

Meets the product standard's requirements.

#### 10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

#### 10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

#### 10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal

## Resources

### Brochures

[eaton-digital-nzm-brochure-br013003en-en-us.pdf](#)

[eaton-feerum-the-whole-grain-solution-success-story-en-us.pdf](#)

### Catalogs

[eaton-digital-nzm-catalog-ca013003en-en-us.pdf](#)

### Declarations of conformity

[DA-DC-03\\_NZM2](#)

### Installation instructions

[eaton-circuit-breaker-voltage-release-nzm2-3-il012141zu.pdf](#)

### Installation videos

[Introduction of the new digital circuit breaker NZM](#)

[The new digital NZM Range](#)

### Technical data sheets

[eaton-nzm-technical-information-sheet](#)

### Wiring diagrams

[eaton-circuit-breaker-nzm-mccb-wiring-diagram.eps](#)

#### elect. effects

Meets the product standard's requirements.

#### 10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

#### 10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.2.7 Inscriptions

Meets the product standard's requirements.

#### 10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.4 Clearances and creepage distances

Meets the product standard's requirements.

#### 10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

#### 10.8 Connections for external conductors

Is the panel builder's responsibility.

#### 10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

#### 10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

#### 10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

#### Electric connection type

Screw connection

#### Fitted with:

Early-make auxiliary contact

#### Number of contacts (normally open contacts)

1

Rated control supply voltage

48 V 50/60 Hz

Rated control supply voltage (Us) at AC, 50 Hz - max

48 V

Rated control supply voltage (Us) at AC, 50 Hz - min

48 V

Rated control supply voltage (Us) at AC, 60 Hz - max

48 V

Rated control supply voltage (Us) at AC, 60 Hz - min

48 V

Suitable for

Motor safety switch

Off-load switch

Connection type

With push in terminal

Voltage type

AC

Rated control supply voltage (Us) at DC - max

0 V

Rated control supply voltage (Us) at DC - min

0 V

Number of contacts (normally closed contacts)

0

Number of contacts (change-over contacts)

0

Undelayed short-circuit release - min

0 A

Undelayed short-circuit release - max

0 A



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)