



EN ISO 20345:2011



ENDURANCE

ROLING BOA®
81374-00L
S3 *CI SRC
Size: 36-48

Weight: 750 gr.

Fit: 11

Working Environment:

Building, Wood-metal carpentry,
Mountains, Multipurpose


FEATURES

UPPER

Grain leather Hydro 1,8-2,0 mm
Reflex insert
Full Grain leather Hydro

LINING

3D Air circulation 320 gr.

ANTISLIP LINING

DUALMICRO

INSOLE

Climaction-Fit 337

TOE CAP

Fiber cap SXT

RESISTANCE TO PERFORATION

KX Antiperforation PS

TYPE

Ankle boot

SOLE

PU DUAL-DENSITY SRC

Two-component PU sole with anti-wear scaff cap and high-comfort in-between insole. Outsole with self-cleaning tread pattern, with a formula designed to ensure greater grip. SRC Antislip standard.

TECHNOLOGIES

Removable Insole

337
climaction fit

Removable anatomic and ergonomic insole. Absorbent and transpiring open-cell foam support. Keeps feet fresh. Specifically-designed thermoforming for exceptional comfort.



Protection elements


RESISTANT
TO 3.0 mm.
NAILS
fibercap sxt

Composite toecap with fiberglass. Resistant to over 200J. Non metal perforation resistant insert to over 1100 N with a 3.0 mm truncated cone nail. Protection over the entire sole of the foot. Flexible and comfortable



Lateral stability

dynamic HC control
 technology

Ergonomic rigid internal structure. It houses the heel into the right seat, adjusting the foot support and control of the ankle sideways movements. It keeps the foot tight to the shoe, allowing the perfect fit.



Torsional stability

STABIL•ACTIVE

Support made of rigid plastic material. It stabilizes the heel bone, the instep and tarsal joints, without altering energy absorption. A support for the natural movement of the foot; it provides comfort and greater stability.




Electrical features



Wire Electricity Discharge

Strip with 4 filaments of carbon fiber, ensuring proven anti-static properties of the footwear over time.



Other


FIT TO GO
FURTHER.™

A patented closing system with a multi coated stainless steel cable. The BOA® Fit System delivers micro-adjustable precision fit, engineered to perform in the toughest conditions.



SRC (SRA+SRB)



SRA CERAMIC + DETERGENT SOLUTION	FLAT ≥0.32	0.52
	HEEL (CONTACT ANGLE °°) ≥0.28	0.48
SRB STEEL + GLYCEROL	FLAT ≥0.18	0.23
	HEEL (CONTACT ANGLE °°) ≥0.13	0.18

EN ISO 20344:2011