

Miniature wheel brush RBU dia. 22x2 mm shank dia. 3 mm stainless steel wire dia. 0.10



**Miniature wheel brush RBU dia. 22x2 mm shank dia. 3 mm
stainless steel wire dia. 0.10**

Item number: [43100752](#)

EAN: [4007220032596](#)

Suitable for light brushing such as deburring, cleaning and polishing.

PFERD TOOLS offers a wide range of miniature brushes for precision work. These can be used on flexible shaft drives, micro motors or electric grinders.

In order to fulfil the particular requirements for working with stainless steel (INOX), PFERD TOOLS uses wire quality 1.4310/1.4301 (V2A) for all INOX brushes. Practical experience from industry has shown that this offers very good corrosion resistance with an optimum tool life. All PFERD TOOLS brushes with INOX filaments are colour-coded in blue and are suitable for use on all stainless steels (INOX), such as V4A. The wire quality 1.4310/1.4301 tends to become ferromagnetic in the case of cold working; i.e. it can be attracted using magnets. The reason for this is a change in the microstructure caused by deformation (e.g. during the wire drawing process). This does not have any impact on the quality and corrosion resistance of the INOX filament. The filament is still resistant to corrosion.

Stainless steel wire (INOX) withstands temperatures up to 450 °C.

Technical information

Dia. external	22 mm
Dia. filament material	0.1 mm
Dia. shank	3 mm
Filament material	Stainless steel wire (INOX)
Length, filament	6 mm
Length, total	46 mm
Max. RPM	12000 RPM
Mounting system	Shank
RPM, optimum	4.000 - 10.000 RPM
Width	2 mm

Advantages

- ✔ Maximum precision and efficiency in work on delicate workpieces.
 - ✔ Enables focused working in hard-to-reach areas.
 - ✔ Very good corrosion resistance.
 - ✔ Creates fine surfaces.
-

Recommendations for use

- ✔ Please observe the recommended rotational speeds.
-

Safety notes

- ✔ When clamping the brush, ensure that the shank is clamped as far into the arbor as possible. This applies in particular for use in the high rotational speed range. The minimum clamping length is 10 mm.
-

Materials that can be worked

- ✔ Aluminium
 - ✔ Bronze
 - ✔ Cobalt-based alloys
 - ✔ Hard non-ferrous metal
 - ✔ High-temperature-resistant materials
 - ✔ Nickel-based alloys (e.g. Inconel and Hastelloy)
 - ✔ Nickel or titanium-based superalloys
 - ✔ Other non-ferrous metals
 - ✔ Soft titanium alloys (tensile strength 500 N/mm²)
 - ✔ Stainless steel (INOX)
 - ✔ Titanium
 - ✔ Titanium alloys
-

Applications

- ✓ Cleaning
 - ✓ Deburring
 - ✓ Derusting
 - ✓ Paint stripping
 - ✓ Removing heat discolouration
 - ✓ Removing oxide layers
 - ✓ Roughening
-

Drive types

- ✓ Flexible shaft drive
 - ✓ Straight grinder
-



August Rüggeberg GmbH & Co. KG
Hauptstraße 13
51709 Marienheide

+49 2264 9-0

+49 2264 9-400

info@pferd.com